

Dimensions

SSOP28 package dimensions

Dimensions and tolerances in mm.

Symbol	Min.	Typ.	Max.	Unit
A			2	mm
A1	0.05			mm
A2	1.65	1.75	1.85	mm
b	0.22		0.38	mm
c	0.09		0.25	mm
D	9.9	10.2	10.5	mm
E	7.4	7.8	8.2	mm
E1	5	5.3	5.6	mm
e		0.65		mm
K	0		10	deg
L	0.55	0.75	0.95	mm

