


# Installation drawing RLC2IC readhead with MS05 scale



Dimensions and tolerances in mm.



\* Minimal distance of reference mark from left edge = 8 mm

\*\* Beginning of measuring length from elastoferrite layer edge = -2 mm

Measuring length = SL - 16 mm