

AM256Q – Angular magnetic encoder IC

Features

- Contactless angular position encoding over 360°
- Ideal for harsh environments due to magnetic sensing
- Complete system-on-chip solution
- 8 bit absolute encoder
- Output options:
 - Incremental
 - Serial SSI
 - Analogue sinusoidal
- Factory optimized linearity
- High rotational speed up to 60,000 rpm
- 5 V power supply
- Low power consumption: 13 mA typical
- Extended operating temperature range (-40 °C to +125 °C)
- SMD package QFN28
- RoHS compliant (lead free)

General description

The AM256Q uses the same technology as the well known AM256 and AM256L integrated circuits but is offered in the compact QFN28 package (6 × 6 mm).

It offers Incremental and Serial (SSI) digital outputs at 8 bit resolution as well as Sinusoidal analogue outputs.

For detailed sensor information, please refer to the AM256 datasheet that can be found on www.rls.si. The AM256Q has the same features, specifications and performance in all respect to the AM256 except that parallel digital outputs are not provided.

Applications

Non-contact position or velocity measurements:

- Motor motion control
- Flow measurement
- Robotics
- Camera positioning
- Front panel switches
- Workshop equipment
- Mobility aids





Fig. 1: AM256Q with magnet

Index

Pin description.....	3
Magnet position.....	3
QFN28 Package Dimensions.....	4
Ordering information	5
Document issues.....	6

Pin description



Magnet position

The magnet can be placed below or above the device. The typical distance between the magnet and the sensors must be 1.8 mm for the recommended magnet.





Fig. 15: Cross section of AM256 with dimensions


Parameter	Symb ol	Min.	Typ.	Max	Unit	Note
Distance sensors – PCB plane	a		0.55		mm	
Distance sensors – chip surface	b		0.45		mm	
Distance sensors – magnet	h	1.6	1.80	2.0	mm	For recommended magnet
Distance magnet – PCB plane	z	2.15	2.35	2.55	mm	For recommended magnet

QFN28 Package Dimensions



Ordering information

1. Angular Magnetic Encoder IC


Part Number	Description
<p>AM256Q</p> 	<p>AM256Q Angular Magnetic Encoder IC with default functionality</p> <p>Outputs:</p> <ul style="list-style-type: none"> - SSI - Incremental - Unbuffered Sine/Cosine <p>QFN28 plastic package</p> <p>Delivered in tubes (48 units per tube)</p>

NOTE: order quantity must be a multiple of 48 (one tube).

NOTE: Can be delivered in reels (special order)

NOTE: magnet must be ordered separately! The Angular Magnetic Encoder IC part number does not include a magnet.

2. Magnet

Part Number	Description
<p>RMM44A2C00</p> 	<p>Diametrically polarized magnet</p> <p>Dimensions: \varnothing 4 mm x 4 mm</p>


Head office

RLS merilna tehnika d.o.o.
 Cesta II. grupe odredov 25
 SI-1261 Ljubljana - Dobrunje

T +386 1 5272100
 F +386 1 5272129
 E mail@rls.si
 www.rls.si

Document issues

Document issue	Date	Changes
03	8. 11. 2007	Changed layout Page 1: Changed the RLS colour to bright yellow Page 5: Corrected the contact information
03	12. 2. 2008	Page 5: Added the ordering information
04	14. 1. 2009	General: New layout

RENISHAW  is our worldwide sales support partner for Magnetic Encoders.

Australia
 T +61 3 9521 0922
 E australia@renishaw.com

Germany
 T +49 7127 9810
 E germany@renishaw.com

The Netherlands
 T +31 76 543 1100
 E benelux@renishaw.com

Sweden
 T +46 8 584 90 880
 E sweden@renishaw.com

Austria
 T +43 2236 379790
 E austria@renishaw.com

Hong Kong
 T +852 2753 0638
 E hongkong@renishaw.com

Poland
 T +48 22 577 1180
 E poland@renishaw.com

Switzerland
 T +41 55 415 5060
 E switzerland@renishaw.com

Brazil
 T +55 11 4195 2866
 E brazil@renishaw.com

Hungary
 T +36 23 502 183
 E hungary@renishaw.com

Russia
 T +7 495 231 1677
 E russia@renishaw.com

Taiwan
 T +886 4 2473 3177
 E taiwan@renishaw.com

Canada
 T +1 905 828 0104
 E canada@renishaw.com

India
 T +91 20 6674 6751
 E india@renishaw.com

Singapore
 T +65 6897 5466
 E singapore@renishaw.com

UK
 T +44 1453 524524
 E uk@renishaw.com

The People's Republic of China
 T +86 10 8448 5306
 E beijing@renishaw.com

Israel
 T +972 4 953 6595
 E israel@renishaw.com

Slovenia (Head Office)
 T +386 1 52 72 100
 E mail@rls.si

USA
 T +1 847 286 9953
 E usa@renishaw.com

Czech Republic
 T +420 5 4821 6553
 E czech@renishaw.com

Italy
 T +39 011 966 1052
 E italy@renishaw.com

South Korea
 T +82 2 2108 2830
 E southkorea@renishaw.com

For all other countries
 Please contact RLS' head office
 T +386 1 52 72 100
 E mail@rls.si

France
 T +33 1 64 61 84 84
 E france@renishaw.com

Japan
 T +81 3 5366 5316
 E japan@renishaw.com

Spain
 T +34 93 663 3420
 E spain@renishaw.com

RLS merilna tehnika d.o.o. has made considerable effort to ensure the content of this document is correct at the date of publication but makes no warranties or representations regarding the content. RLS merilna tehnika d.o.o. excludes liability, howsoever arising, for any inaccuracies in this document.