


Orbis BBM

BiSS C Register Access

Abstract: The BiSS C interface implemented in Orbis supports bidirectional communication in register access mode. The readhead can be configured by the user. The implementation is compliant with BiSS C (also Standard Encoder Profile, known as “BP3”), which is used to group linear and rotary encoders. Details on BiSS register access and BP3 can be found on the [BiSS website](#).

User implementation: bidirectional BiSS can be configured by the user according to the BiSS documentation provided by iC-Haus. Alternatively, it is also possible to use the iC-MB4 chip by iC-Haus, which translates the high-level commands on the SPI bus into BiSS. The easiest way is to use the E201-9B interface from RLS including the corresponding software.

Related products



Orbis Battery Backup
Multiturn off-axis absolute
magnetic encoder



E201-9B USB interface

General information

BiSS EDS banks

Bank	Address	Symbol	Description	Data type	Unit	Value
	0x00	EDS_VER	EDS version	U8	-	1
	0x01	EDS_LEN	EDS length	U8	Banks	2
	0x02	USR_STA	Bank address USER start	U8	-	255
	0x03	USR_END	Bank address USER end	U8	-	1
	0x04	TMA	Min. permitted clock period	U8	1 ns	200
	0x05	TO_MIN	Min. BiSS timeout	U8	250 ns	52
	0x06	TO_MAX	Max. BiSS timeout	U8	250 ns	60
	0x07	TOS_MIN	Min. BiSS timeout_S	U8	25 ns	0
	0x08	TOS_MAX	Max. BiSS timeout_S	U8	25 ns	0
	0x09	TCLK_MIN	Min. sampling period adaptive timeout	U8	25 ns	0
	0x0A	TCLK_MAX	Max. sampling period adaptive timeout	U8	25 ns	0
	0x0B	TCYC	Min. cycle time	U8	250 ns	100
	0x0C	TBUSY_S	Max. Processing time SCD	U8	250 ns	0
	0x0D	BUSY_S	Max. Processing time SCD in clocks	U8	TMA	13
0	0x0E-0x0F	PON_DLY	Max. »power on delay« until control communication is available	U16	1 ms	200
	0x10	DC_NUM	Number of channels in this device	U8	-	1
	0x11	SL_NUM	Area of validity for this EDS (number of slave addresses)	U8	-	1
	0x12	SL_OFF	Memory location for this EDS (slave ID within this device)	U8	-	0
	0x13		Reserved	U8		0
	0x14	BANK1	Bank address for content description of data channel 1 (profile EDS)	U8	-	1
	0x15	DLEN1	Data length for data channel 1	U8	Bit	32
	0x16	FORMAT1	Data format for data channel 1	U8	Bit	2
	0x17	CPOLY1	CRC polynomial (8:1) for data channel 1	U8	-	0x21
	0x18-0x33		Reserved	U8		0
	0x34	BC_OFF	Bus coupler control location for this device (slave ID within this device)	U8	-	0
	0x35-0x3E		Reserved	U8		0
	0x3F	CHKSUM	Checksum (sum of all bytes within this bank)	U8	-	xx

Bank	Address	Symbol	Description	Data type	Unit	Value
	0x00	BP_VER	BiSS profile 3 version	U8	-	1
	0x01	BP_LEN	Length of this profile	U8	Banks	1
	0x02-0x03	BP_ID	Profile identification BP3 (content also available in addresses 0x42 and 0x43)	U16	-	0x6220
	0x04	PROFILE_FB1	Feedback bit 1 (nError = 1)	U8	-	1
	0x05	PROFILE_FB2	Feedback bit 2 (nWarning = 2)	U8	-	2
	0x06	PROFILE_PON_PDL	Max. »power on delay« until position data is available	U8	ms	200
	0x07		Reserved	U8		0
	0x08	PROFILE_EN_TYP	Encoder type (rotary = 0)	U8	-	0
	0x09	PROFILE_POS_NUM	Position value (1 position)	U8	-	1
	0x0A	PROFILE_MT_LEN	Data length MULTITURN	U8	Bit	16
	0x0B	PROFILE_MT_FMT	Data format MULTITURN	U8	-	1
	0x0C	PROFILE_CO_LEN	Data length COARSE	U8	Bit	0
	0x0D	PROFILE_CO_FMT	Data format COARSE	U8	-	0
	0x0E	PROFILE_FL_LEN	Data length FINE	U8	Bit	14
	0x0F	PROFILE_FL_FMT	Data format FINE	U8	-	0
	0x10-0x13	PROFILE_MT_CNT	Number of distinguishable revolutions	U32	Count	65536
	0x14-0x17	PROFILE_SIP_CNT	Number of signal periods per revolution	U32	PPR	1
	0x18-0x1B	PROFILE_SIP_RES	Resolution factor per signal period (LSB of interpolation)	U32	Count	16384
1	0x1C-0x1F	PROFILE_CPOLY	CRC polynomial (32:1 of 0x43)	U32	-	0x21
	0x20-0x23	PROFILE_CSTART	CRC start value	U32	-	0
	0x24-0x25	PROFILE_ABS_ACU	Absolute accuracy	U16	LSB/2	28
	0x26-0x27	PROFILE_REL_ACU	Relative accuracy	U16	LSB/2	0
	0x28-0x29	PROFILE_SPD_ACU	Angular speed depending accuracy	U16	LSB/2	0
	0x2A-0x2B	PROFILE_HYST	Hysteresis	U16	LSB/2	2
	0x2C-0x2D	PROFILE_SPD_MAX	Max. revolution speed	U16	1/min	15k **
	0x2E-0x2F	PROFILE_ACC_MAX	Max. revolution acceleration	U16	1/min ²	0
	0x30-0x31	PROFILE_TMP_MIN	Min. operating temperature	U16	K	233*
	0x32-0x33	PROFILE_TMP_MAX	Max. operating temperature	U16	K	378*
	0x34-0x35	PROFILE_VLT_MIN	Min. operating voltage	U16	mV	4500
	0x36-0x37	PROFILE_VLT_MAX	Max. operating voltage	U16	mV	5500
	0x38-0x39	PROFILE_CUR_MAX	Max. current consumption	U16	mA	70
	0x3A-0x3E		Reserved	U8		0
	0x3F	CHKSUM	Checksum (sum of all bytes within this bank)	U8	-	xx

All parameters from EDS banks are read-only.

* Parameter value depends on actual part number.

** Warning triggered at 15k.

Encoder identification bank

Bank	Address	Data type	Access	Default value	Description
2	0x00–0x0F	16 x U8	R	*	RLS serial number (ASCII characters)
	0x10–0x13	U8	R	0	Reserved
	0x14–0x27	20 x U8	R	*	RLS part number (ASCII characters)
	0x28–0x29	U16	R	0x04	FW major version
	0x2A–0x2B	U16	R	0x04	FW minor version
	0x2C–0x2D	U16	R	0x08	FW hotfix version
	0x2E–0x31	U32	R	*	FW build version
	0x32–0x35	4 x U8	R	*	FW version short hash
	0x36–0x3E	U8	R	0	Reserved
	0x3F	U8	R	xx	Checksum (sum of all bytes within this bank)

* Most values of parameters in identification bank depend on actual part.

Encoder configuration bank

Bank	Address	Data type	Access	Value in effect	Default value	Description
3	0x00–0x03	U32	RW	Immediate	0	Position offset*
	0x04–0x07	U32	RW	Power-on	252	Position filter value
	0x08–0x0B	U32	RW	Power-on	4000	Position filter speed
	0x0C–0x0F	U32	RW	Power-on	252	Velocity filter value
	0x10	U8	RW	Power-on	0	Maximum acceleration **
	0x11–0x13	U8	R		0	Reserved
	0x14–0x17	U32	RW	Immediate	0	Multiturn counter preset
	0x18–0x3D	U8	R		0	Reserved
	0x3E	U8	RW	After "c" command	0x5A	Write protect lock
	0x3F	U8	R		xx	Checksum (sum of all bytes within this bank)

* Maximum allowed value is determined from encoder resolution.

** Value Notes

Value	Notes
0	157 rad/s ² acceleration
1	1570 rad/s ² acceleration
2	Infinite acceleration (limited by maximum speed of 900 rpm)

The maximum speed of 900 rpm applies to all acceleration settings (0–2).
Changing the default acceleration value may increase power consumption.

Self-calibration bank

Bank	Address	Data type	Access	Value in effect	Default value	Description
	0x00-0x03	U32	R		0	Self-calibration status
	0x04-0x0B	U8	R		0	Reserved
4	0x0C	U8	RW	Immediate	10	Calibration timeout in seconds
	0x0D-0x3E	U8	R		0	Reserved
	0x3F	U8	R		xx	Checksum (sum of all bytes within this bank)

PRELIMINARY

Direct access registers

Address	Data type	Access	Value in effect	Default value	Description
0x40	U8	RW	Immediate	0	Bank select
0x41	U8	R		0	EDS bank
0x42-0x43	U16	R		0x6220	Profile ID
0x44-0x47	U32	R		*	Serial number (encoded)
0x48	U8	RW	Immediate	255	Key register
0x49	U8	RW	Immediate	255	Command register
0x4A-0x4D	U32	R		0	Encoder detailed status (see chapter Encoder operating parameters)
0x4E-0x4F	S16	R		**	Sensor temperature in °C
0x50-0x53	U32	R		**	Signal level
0x54-0x57	S32	R		**	Measured velocity in 0.1 rpm
0x58-0x5B	U32	R		0	Persistent detailed status
0x5C	U8	R		0	Parameter access status register - table A
0x5D	U8	R		0	Multiturn status
0x5E-0x5F	U16	R		**	Battery voltage in mV
0x60-0x73	U8	R		0	Reserved
0x74-0x77	U32	R		Same as in Identification bank	Major FW version
0x78-0x7D	U8	R		*	Device ID
0x7E-0x7F	U16	R		0x5253	Manufacturer ID

* Parameter value depends on actual part.

** Parameter value changes during operation.

Table A

Bit	Description
0	Write access denied
1	Value out of range
2-5	Reserved
6	Command fetched and executed
7	Write lock active

Bank switching

BiSS registers are grouped into the banks in size of 64 bytes. Each register in each bank can be accessed with the address from 0x00 to 0x3F. Before access to a certain bank, it has to be selected in the bank select register, which is mapped to address 0x40.

Read access

All registers in Orbis BBM memory are readable. Read access also supports sequential reading. It is possible to read up to 64 bytes forward from initialized read address.

Write access

Writable registers in Orbis BBM memory are presented in table »Memory map«. All registers can be write-protected if write access is locked by the user, except of bank select register. Sequential write access is available in all banks.

Further information on bank switching and detailed descriptions of sequential read and write access can be found in the iC-Haus documentation.

Encoder operating parameters

Address	Data type	Access	Description
0x4A-0x4D	U32	R	Encoder status (see table below)
0x4E-0x4F	S16	R	Sensor temperature in °C
0x50-0x53	U32	R	Signal level
0x54-0x57	S32	R	Rotational speed in 0.1 rpm
0x00-0x03	U32	R	Self-calibration status (bank 4)

Encoder status (address 0x4A–0x4D)

Persistent detailed status (address 0x58–0x5B)

Detailed status		
b15	Warning	Multiturn warning. Multiturn is valid but may not be valid after power cycle. See multiturn status register.
b14	Warning	Temperature out of range. The readhead temperature is out of specified range.
b13	Warning	Signal amplitude low. The distance between the readhead and the magnet is too large.
b12	Warning	Signal amplitude too high. The readhead is too close to the magnet or an external magnetic field is present. There is also a possibility that the magnet is touching the readhead. It is strongly recommended that the user checks the encoder mounting immediately after this warning gets set.
b11	Warning	Multiturn is valid and will also be valid after power cycle, however the limit of reliable operation is being approached. See multiturn status register.
b10	Warning	Rotational speed exceeds the limit.
b9	Error	Multiturn error. Multiturn is not valid. It is caused by any other status that has Error in Error/warning column. Check multiturn status register on BBM.
b8	Error	Acceleration error. The position data changed unexpectedly or too fast. A stray magnetic field is present or metal particles are present between the readhead and the magnet.
b7	Reserved	
b6	Error	Signal lost. The readhead is out of alignment with the magnet or the magnet is damaged.
b5	Error	Signal amplitude too high. An external magnetic field is present.
b4	Error	System error. Malfunction inside the circuitry. To reset the system error bit try to cycle the power supply on both battery and main supply. If the issue persists, contact RLS .
b3	Reserved	
b2	Reserved	
b1	Error	Internal communication error. Check environment for EMI. To reset the error bit, cycle the power supply on both battery and main supply. If the issue persists, contact RLS .
b0	Reserved	

Register Persistent detailed status (address 0x58–0x5B) accumulates all the status bits that were active during encoder operation, in every internal encoder cycle, even if communication is not active.

Format of the data is same as standard Detailed status register.

Clearing the Persistent status register is performed by writing value 0xCD into Key register (0x48), immediately followed by writing value ASCII 'b' (0x62) into Command register (0x49).

Sensor temperature (address 0x4E–0x4F)

Temperature of the sensor in °C. This value is typically 10 °C to 15 °C higher than ambient. Tolerance of the readout is ±7 °C.

Signal level (address 0x50–0x53)

Signal level information can be used to estimate encoder ride height. Value is proportional to the distance between the sensor and the magnet.

	BR10	BR20	BR30	Error/warning	Description		
Amplitude limits [cnt]	8700000	12400000	7200000	ERROR	magnet too far	↑	Nominal
	10300000	14500000	8700000	WARNING			
	25000000	30800000	25000000	WARNING	magnet too close	↓	
	/	38100000	28000000	ERROR			

Rotational speed (address 0x54–0x57)

Encoder rotational speed in 0.1 rpm.

Self-calibration status (address 0x00–0x03)

See chapter Self-calibration on page [10](#).

Orbis BBM programming

Position offset (encoder zero position), multiturn counter and register write protection can be programmed to the Orbis readhead. Additional to this, the readhead can be self-calibrated or reset to the factory defaults.

Numbers written into registers take effect immediately, with some exceptions. See “value in effect” column in registers description tables.

Command execution

To execute a command following sequence must be used:

- Write value 0xCD to Key register at address 0x48
- Write command byte to Command register at address 0x49

Write to key and command register must be sequential. No other register access should take place in between, otherwise command will not be executed. Any other register access after correct key is entered, invalidates key value and the command write procedure has to be repeated.

After each command is fetched by encoder, communication is disabled during command execution.

Communication is enabled only after command has executed which can last up to 100 ms (for exact times see the table below).

During this time encoder will not respond to communication requests.

Supported commands

Command	Command [hex]	Typ. execution time [ms]	Description
'A'	0x41	set with parameter	Self-calibration start
'b'	0x62	1	Persistent detailed status reset
'c'	0x63	70	Save current configuration to non-volatile memory
'r'	0x72	70	Configuration reset to factory defaults
'm'	0x6D	30	Validate the multiturn counter

Programming a multiturn counter greater than 65535 (unsigned) is discarded.

Multiturn counter

Multiturn counter is mapped to the registers 0x14, 0x15, 0x16, 0x17 of bank 3 in Big Endian format. User must first write separate bytes of a new multiturn counter to these addresses. Afterwards, they can be read to verify the proper write operation. At this moment, new multiturn counter is not active yet. To validate it, user must first unlock the command register by writing the KEY. Next register access must be a write to the command register to validate the multiturn counter value. Validation procedure has to be done twice.

KEY: value 0xCD to address 0x48

Command for validation of multiturn counter: ASCII 'm' (0x6D) to address 0x49

Programming of multiturn counter larger than 65535 (unsigned) is discarded.

Position offset (encoder zero position)

Position offset is mapped to the registers 0x00, 0x01, 0x02, 0x03 of bank 3 in a big-endian format. User must write separate bytes of a new position offset in counts to these addresses. Afterwards, they can be read to verify the proper write operation.

If the absolute applied position offset is larger than the actual encoder resolution, value will not get updated.

After changing zero position for a bigger value, acceleration error might appear.
After every setting of a new position offset, verify or adjust multiturn counter value (if present).

To store new values into non-volatile memory use the following sequence:

KEY: value 0xCD to address 0x48

Command for saving programmed data to a non-volatile memory: ASCII 'c' (0x63) to address 0x49

Saving parameters to non-volatile memory takes 70 ms. During this time position is not valid. Multiturn counter should be written only when the encoder's readhead and magnet are stationary.

Self-calibration

The Orbis BBM encoder supports an integrated self-calibration procedure, recommended after mechanical installation of the readhead. This process compensates for mounting misalignment, enhancing overall system accuracy.

Procedure

1. Unlock command access
Write the key value 0xCD to the Key Register (0x48).
2. Start self-calibration
Immediately write command 0x41 to the Command Register (0x49).

During self-calibration

- BiSS interface is disabled — the encoder ignores all incoming clock cycles and does not respond.
- LED indication signals completion:
 - Green flashing (3 s) – calibration successful
 - Red flashing (3 s) – calibration failed
- After indication, BiSS communication is automatically restored.

Status monitoring

- Before initiating calibration, read Bank 4, Register 0x00, and store the value of the 2-bit calibration counter (bits [1:0]).
- After calibration, either:
 - Observe the LED for result, or
 - If the LED is not visible, wait up to 10 seconds or poll the BiSS interface for reactivation.
- Re-read Bank 4, Register 0x00:
 - A counter increment confirms that self-calibration has completed.
 - Status flags in the same register provide success or failure information.

Additional calibration diagnostics and result codes are available in Bank 4. When the self-calibration counter has increased by 1 (compared to the previously read value), the self-calibration function has been completed. Additional data from the self-calibration is available in bank 4.

Address	Type	Range	Units	Meaning / usage
INPUT				
0x0C, bank 4	U8	1–40	s	Calibration timeout
0x48	U8	0xCD	–	Key
0x49	U8	0x41	–	Command
OUTPUT, bank 4				
0x00	U8		bit	Status – see table below

Self-calibration status register

Bit	Meaning
b21	Error – parameters could not be saved to non-volatile memory (system fault).
b20	Indication – error map table is not default (self-calibration was successfully performed). Comparison is executed at power-up and at every command »Save to NVRAM«.
b19	Reserved
b18	Reserved
b17	Reserved
b16	Reserved
b15	Reserved
b14	Reserved
b13	Error – eccentricity or ride height are very high.
b12	Error – numerical error during data processing.
b11	Reserved
b10	Reserved
b9	Error – encoder is in error state while calibration is started – aborted.
b8	Timeout – encoder did not complete full revolution (or partial arc) in preset time.
b7	Reserved
b6	Error
b5	Reserved
b4	Confirmation – self-calibration successfully completed.
b3	Reserved
b2	Reserved
b1:b0	Counter is incremented at the end of self-calibration procedure.

When self-calibration is completed without error, the new parameters are automatically stored in non-volatile memory and no further command is required.

Dynamic filtering

The Orbis BBM encoder uses dynamic low-pass filters to reduce noise in the calculated position value.

The default values are suitable for most applications. However, in some extreme cases, fine tuning is required to achieve optimum performance. For example, in precise applications with low speed and acceleration, the filtering can be increased to increase the resolution.

In contrast, fast and dynamic applications may require a reduction in filtering to reduce delay and increase the bandwidth.

Filter settings


Settings are present in bank 3 – encoder configuration bank.

Address	Name	Default	Range	Description
0x04–0x07	Position filter value	252	0–254	Maximum value of Position Filter when encoder is standstill. 0 = filter disabled
0x08–0x0B	Position filter speed	4000	0–10,000	Encoder speed when Position Filter is switched off. Below 100: filter is constant
0x0C–0x0F	Velocity filter value	252	0–254	Value of Velocity Filter. 0 = filter disabled

Position filter

Encoder position value, from every internal encoder cycle, is passed through the low-pass filter. This gives smoother position value and increased resolution when encoder speed is low or decelerating.

Increased Value parameter increases filter strength and reduces cut-off frequency. This value is used when encoder is standstill. With increasing rotational speed, filter is linearly reduced. When rotational speed is equal or higher than Speed parameter, filter is switched off.



Velocity filter

Internally calculated velocity (rotational speed) is passed through the low-pass filter. This gives smoother position value on BiSS interface. Increased Value parameter increases filter strength and reduces cut-off frequency. Filter is constant and not dependent on the rotational speed. Speed parameter is not used and is set to zero.

Changing filter values may cause encoder or closed control loop to become unstable. Use with caution and evaluate all possible situations before keeping the new values.

To store new values into non-volatile memory use the following sequence:

KEY: value 0xCD to address 0x48

Command for saving programmed data to a non-volatile memory: ASCII 'c' (0x63) to address 0x49.

Saving parameters to non-volatile memory takes 70 ms. During this time position is not valid. Mutiturn counter should be written only when the encoder's readhead and magnet are stationary.

Reset to factory default

Reset to factory default will set all programmed parameters to default ones. User must first unlock the command register by writing the KEY. Next register access must be a write of the Command to reset readhead to the factory defaults.

KEY: value 0xCD to address 0x48

Command to reset readhead to the factory defaults: ASCII 'r' (0x72) to address 0x49

Saving parameters to non-volatile memory takes 70 ms. During this time position is not valid. Mutiturn counter should be written only when the encoder's readhead and magnet are stationary.

After locking the write access, the encoder cannot be reset to the factory default.

Write protection

Write protection can be used to lock the write access of any writable register in Orbis memory map, except of Bank select register. It is mapped to the register 0x3E of bank 3. Its default value is 0x5A. To lock the write access, user should write any value other than 0x5A. After that, the write access of any register, except of Bank select, will be refused. All registers will behave as a non-writable registers.

Command for saving programmed data to a non-volatile memory: ASCII 'c' (0x63) to address 0x49.

Saving parameters to non-volatile memory takes 70 ms. During this time position is not valid. Mutiturn counter should be written only when the encoder's readhead and magnet are stationary.

After locking the write access, the readhead cannot be programmed anymore. All registers are still readable.

Head office

RLS Merilna tehnika d. o. o.

Poslovna cona Žeje pri Komendi
Pod vrbami 2
SI-1218 Komenda
Slovenia

T +386 1 5272100
E mail@rls.si
www.rls.si

Global support

Visit our [website](#) to contact your nearest sales representative.

Document issues

Issue	Date	Page	Description
1	19. 12. 2025	-	New document

This product is not designed or intended for use outside the environmental limitations and operating parameters expressly stated on the product's datasheet. Products are not designed or intended for use in medical, military, aerospace, automotive or oil & gas applications or any safety-critical applications where a failure of the product could cause severe environmental or property damage, personal injury or death. Any use in such applications must be specifically agreed to by seller in writing, and is subject to such additional terms as the seller may impose in its sole discretion. Use of products in such applications is at buyer's own risk, and buyer will indemnify and hold harmless seller and its affiliates against any liability, loss, damage or expense arising from such use. Information contained in this datasheet was derived from product testing under controlled laboratory conditions and data reported thereon is subject to the stated tolerances and variations, or if none are stated, then to tolerances and variations consistent with usual trade practices and testing methods. The product's performance outside of laboratory conditions, including when one or more operating parameters is at its maximum range, may not conform to the product's datasheet. Further, information in the product's datasheet does not reflect the performance of the product in any application, end-use or operating environment buyer or its customer may put the product to. Seller and its affiliates make no recommendation, warranty or representation as to the suitability of the product for buyer's application, use, end-product, process or combination with any other product or as to any results buyer or its customer might obtain in their use of the product. Buyer should use its own knowledge, judgment, expertise and testing in selecting the product for buyer's application, end-use and/or operating environment, and should not rely on any oral or written statement, representation, or samples made by seller or its affiliates for any purpose. EXCEPT FOR THE WARRANTIES EXPRESSLY SET FORTH IN THE SELLER'S TERMS AND CONDITIONS OF SALE, SELLER MAKES NO WARRANTY EXPRESS OR IMPLIED WITH RESPECT TO THE PRODUCT, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE, WHICH ARE DISCLAIMED AND EXCLUDED. All sales are subject to seller's exclusive terms and conditions of sale which, where the seller is (a) RLS Merilna tehnika d. o. o. , are available at <https://www.rls.si/eng/salesterms>, (b) Renishaw, Inc., are available at <https://www.renishaw.com/legal/en/-42186>, or (c) another person, are available on request, and in each case, are incorporated herein by reference, and are the exclusive terms of sale. No other terms and conditions apply. Buyer is not authorized to make any statements or representations that expand upon or extend the environmental limitations and operating parameters of the products, or which imply permitted usage outside of that expressly stated on the datasheet or agreed to in writing by seller.

RLS Merilna tehnika d. o. o. has made considerable effort to ensure the content of this document is correct at the date of publication but makes no warranties or representations regarding the content. RLS Merilna tehnika d. o. o. excludes liability, howsoever arising, for any inaccuracies in this document. © 2025 RLS d. o. o.