

RM22 series non-contact rotary encoders

EMC compliance



This encoder system conforms to the relevant harmonised European standards for electromagnetic compatibility as detailed below.

BS EN 61326

Further information




For further information relating to the installation of RM22 encoders see also the RM22 data sheet (part number RM22D01). This can be downloaded from our website www.rls.si and is also available from your local representative.

This document may not be copied or reproduced in whole or in part, or transferred to any other media or language, by any means without the written prior permission of RLS d.o.o. The publication of material within this document does not imply freedom from the patent rights of RLS d.o.o.

Disclaimer

Considerable effort has been made to ensure that the contents of this document are free from inaccuracies and omissions. However, RLS merilna tehnika d.o.o. makes no warranties with respect to the contents of this document and specifically disclaims any implied warranties. RLS merilna tehnika d.o.o. reserves the right to make changes to this document and to the product described herein without obligation to notify any person of such changes.

Handling



General specifications

Power supply 5 V \pm 5%

RM22 A/B/P/V 20 mA
RM22 I/S 23mA - 9bit. 35mA for all other resolutions

NOTE: Current consumption figures refer to unterminated encoders. When terminated with 120 Ω , RM22 S will draw an additional 25 mA, while RM22 I will draw an additional 25 mA per channel pair (A+, A-).

Sealing

IP64 (IP68 option available)

Operating temperature

RM22 IB -25 °C to +85 °C
RM22 S/P/V/A -40 °C to +125 °C

Humidity storage

95% maximum relative humidity (non-condensing) (BS EN 61010-1)

operating

80% maximum relative humidity (non-condensing) (BS EN 61010-1)

Acceleration operating

500 m/s² BS EN 60068-2-7:1993 (IEC 68-2-7:1983)

Shock non-operating

1000 m/s², 6 ms, 1/2 sine
BS EN 60068-2-27:1993 (IEC 68-2-27:1987)

Vibration operating

100 m/s², 55 Hz to 2000 Hz
BS EN 60068-2-6:1996 (IEC 68-2-6:1995)

Mass

RM22 inc. 1 m cable no connector 48 g
magnetic actuator 12 g

Cable


Outside diameter 5 mm
Maximum cable length 3 m (RM22A),
20 m (RM22B), 20 m (RM22V)
30 m (RM22P), 50 m (RM22I),
100 m (RM22S at 1MHz).

IMPORTANT: Power to RM22 encoders must be supplied from a DC SELV supply complying with the essential requirements of EN (IEC) 60950 or similar specification.

The RM22 series encoders have been designed to the relevant EMC standards, but must be correctly integrated to achieve EMC compliance. In particular, attention to shielding arrangements is critical.


RM22 dimensions

Dimensions and tolerances in mm




*Hole diameter for nominal shaft size

RM22 installation drawing




**Nominal shaft size with tolerance h7

Connections




RM22 P



15 pin D plug

Pin Nr.	Function	Wire colour	Pin Nr.	Function	Wire colour
1	Shield-see connection diagram		9	D2	Black
2	D8	White	10	D1	Violet
3	D7	Brown	11	D0	Orange
4	D6	Green	12	NC	-
5	D5	Yellow	13	NC	-
6	D4	Grey	14	LE	Clear
7	D3	Pink	15	GND	Blue
8	V _{dd}	Red			

RM22 S/I/A



9 pin D plug

Pin Nr.	RM22 S		RM22 I		RM22 A		RM22 B		RM22 V	
	Function	Wire colour	Function	Wire colour	Function	Wire colour	Function	Wire colour	Function	Wire colour
1	Shield-see connection diagram		Shield-see connection diagram		Shield-see connection diagram		Shield-see connection diagram		Shield-see connection diagram	
2	Clock	White	Z	White	V _A	Green	V _A +	Green	NC	-
3	Clock-	Brown	B	Green	V _B	Brown	V _B +	Brown	V _{out}	Green
4	NC	-	A	Grey	NC	-	NC	-	NC	-
5	V _{dd}	Red	V _{dd}	Red	V _{dd}	Red	V _{dd}	Red	V _{dd}	Red
6	Data	Green	Z-	Brown	NC	-	V _A -	Yellow	NC	-
7	Data-	Yellow	B-	Yellow	NC	-	V _B -	White	NC	-
8	NC	-	A-	Pink	NC	-	NC	-	NC	-
9	GND	Blue	GND	Blue	GND	Blue	GND	Blue	GND	Blue