

RTB20

High Resolution Magnetic Encoder

The RTB20 high-resolution magnetic encoder features 18-bit resolution in an ultra-compact Ø20 mm encoder board, delivering exceptional precision in the smallest footprint. Its compact and lightweight design makes it ideal for applications such as printing, industrial automation, motor control and instrumentation.









Why choose

RTB20?

FEATURES:

- Based on TMR sensor
- ✓ Incremental resolution up to 18 bit
- UVW signals for commutation up to256 pole pairs
- Zeroing function

BENEFITS:

- Simple and fast installation
- ✓ Non-contact, frictionless design
- ✓ Miniature design, Ø20 mm
- ✓ Long-term reliability
- ✓ No hysteresis



AUTOMATION



MOTOR CONTROL



MEDICAL



AGRICULTUR



PACKING

RLS d. o. o.

Poslovna cona Žeje pri Komendi Pod vrbami 2 SI-1218 Komenda Slovenia T: +386 1 5272100 E: mail@rls.si www.rls.si


A RENISHAW associate company

RTB20 technical specifications

SYSTEM DATA	
Power supply	$Vdd = 5 V \pm 5\%$
Current consumption	Typ. 40 mA (not loaded)
Maximum speed	30,000 rpm
Incremental outputs	A, B, Z line driver (RS422)
Incremental resolutions	Programmable up to 18 bit, decimal to 250k CPR
Commutation outputs	U, V, W single ended
Pole pairs for commutation	Programmable from 1 to 256
ENVIRONMENTAL DATA	
Operating temperature	-40 °C to +105 °C (Limited by connector)

Connections

Connector on board - Molex 501568-1107 (11 pin)



RLS d. o. o. has made considerable effort to ensure the content of this document is correct at the date of publication but makes no warranties or representations regarding the content. RLS d. o. o. excludes liability, howsoever arising, for any inaccuracies in this document. © 2024 RLS d. o. o.



RLS d. o. o. Poslovna cona Žeje pri Komendi Pod vrbami 2 SI-1218 Komenda Slovenia **T:** +386 1 5272100 **E:** mail@rls.si

www.rls.si