


FlexIN™

Magnetic Scale System for Large Diameters



FlexIN is a rubber-supported magnetic scale system with built-in tensioning mechanism compatible with LM10 or LM15 incremental encoders. It is designed for installation onto large shafts as an element of the position and speed control loop. The compact readhead has wide installation tolerances and offers industry standard output types and a reference pulse for relative position. The non-contact measuring principle ensures high reliability in demanding applications.



Why choose FlexIN?

FEATURES:

- ✓ Rubber spring profile supported scale with built-in tensioning mechanism
- ✓ For external diameter installation
- ✓ For diameters from 350 mm to 2,500 mm

BENEFITS:

- ✓ Full circle measurement
- ✓ Maximum rotational speed 210 rpm at 1 m
- ✓ Large diameter tolerance ± 0.2 mm
- ✓ Temperature range from -20 °C to $+85$ °C
- ✓ Substrate thermal expansion compensation



WIND
TURBINES



RADIO
TELESCOPE



SOLAR
PANELS



CT
SCANNING



HARSH
ENVIRONMENT

RLS d. o. o.
Poslovna cona Žeje pri Komendi
Pod vrbami 2
SI-1218 Komenda
Slovenia

T: +386 1 5272100
E: mail@rls.si

www.rls.si

A **RENISHAW** associate company


FlexIN key specifications

READHEAD	LM10	LM15			
Substrate diameter	350 mm to 2,500 mm	350 mm to 2,500 mm			
Number of magnetic periods (depends on the diameter)	282 – 2,755	113 – 1,102			
Accuracy at 1 m diameter	< ±0.02°	< ±0.035°			
Resolution	Up to 13 bits per pole	Up to 13 bits per pole			
Hysteresis	< 3 µm at 0.3 mm ride height	< 12.5 µm at 1 mm ride height			
Reference mark	Single, periodic	Single, periodic			
Maximum permissible speed (mechanical limit)	rpm = 210/D* [m]	rpm = 210/D* [m]			
Operating temperature	-20 °C to +85 °C	-20 °C to +85 °C			
Installation tolerances:	No reference	Magnetised reference	No reference	Magnetised reference	
	Lateral offset	±1 mm	±0.7 mm	±1 mm	±0.7 mm
	Ride height	0.3 mm; +1.2/-0.2 mm	0.3 mm; +0.7/-0.2 mm	0.5 mm; +3.5/-0.4 mm	0.5 mm; +2.5/-0.4 mm

* D represents the outside diameter of assembled scale in mm.

FlexIN with LM10/15 readhead dimensions

Dimensions and tolerances in mm



RLS d. o. o. has made considerable effort to ensure the content of this document is correct at the date of publication but makes no warranties or representations regarding the content. RLS d. o. o. excludes liability, howsoever arising, for any inaccuracies in this document. © 2024 RLS d. o. o.



RLS d. o. o.
 Poslovna cona Žeje pri Komendi
 Pod vrbami 2
 SI-1218 Komenda
 Slovenia

T: +386 1 5272100
E: mail@rls.si
www.rls.si

A **RENISHAW** associate company