

RM22 rotary magnetic encoder with AM4096



The RM22 is a compact, high-speed rotary magnetic encoder designed for use in harsh environments. The non-contact two part design removes the need for seals or bearings ensuring long-term reliability and simple installation.

The encoder comprises a magnetic actuator and a separate encoder body. Rotation of the magnetic actuator is sensed by a custom encoder chip within the body, and processed to give the required output format.

The encoder chip processes the signals received to provide resolutions to 12 bit (4,096 positions per revolution) with high operational speeds. Output signals are provided in industry standard absolute, incremental, analogue or linear formats.

The compact encoder body is just 22 mm in diameter and provides dirt immunity up to IP68.

The RM22 can be used in a wide range of applications including marine, medical, print, converting, industrial automation, metal working, motor control and instrumentation.

Product range

RM221C


Incremental with 8 to 1,024 pulses per revolution (32 to 4,096 counts per revolution with x 4 evaluation)

RM22SC

Synchro serial interface (SSI) with 32 to 4,096 positions per revolution



- Excellent immunity to IP68
- Non-contact, frictionless design
- High speed operation to 30,000 rpm
- Compact - 22 mm diameter body
- Absolute - to 12 bit (4,096 positions per revolution)
- Industry standard absolute, incremental, analogue and linear output formats
- Accuracy to $\pm 0.5^\circ$
- Simple installation
- RoHS compliant (lead free) - see Declaration of conformity

Storage and handling




IMPORTANT: Power to RM22 encoders must be supplied from a DC SELV supply complying with the essential requirements of EN (IEC) 60950 or similar specification.

The RM22 series encoders have been designed to the relevant EMC standards, but must be correctly integrated to achieve EMC compliance. In particular, attention to shielding arrangements is critical.



Connections



Pin nr.	RM22IC		RM22SC	
	Function	Wire colour	Function	Wire colour
1	Shield - see connection diagram			
2	Z	White	Clock	White
3	B	Green	Clock-	Brown
4	A	Grey	NC	-
5	V _{dd}	Red	V _{dd}	Red
6	Z-	Brown	Data	Green
7	B-	Yellow	Data-	Yellow
8	A-	Pink	NC	-
9	GND	Blue	GND	Blue


Operating and electrical specifications

EMC compliance	EN 61326
Cable	Outside diameter 5 mm
Connector options	D' type connector - 9 way Flying lead
Mass	Encoder unit 1 m cable (no connector): 48 g; magnetic actuator: 12 g
Environmental sealing	IP64 (IP68 optional) EN 60529


Dimensions

Dimensions and tolerances in mm


Radial cable exit



Axial cable exit



Magnetic actuator




* Hole diameter for nominal shaft size.




Clockwise (CW) rotation of magnetic actuator.

Installation drawing



** Nominal shaft size with tolerance h7.




RM22IC – Incremental, RS422

Square wave differential line driver to RS422

Power supply	$V_{dd} = 5\text{ V} \pm 5\%$
Current consumption	Max. 35 mA
Output signals	A, B, Z, A-, B-, Z- (RS422)
Accuracy	$\pm 0.5^\circ$
Hysteresis	0.18°
Resolutions	32, 64, 128, 256, 512, 1,024, 2,048, 4,096 cpr
Maximum speed	60,000 rpm for resolutions up to 1,024 cpr 30,000 rpm for 2,048 and 4,096 cpr
Temperature	$-40\text{ }^\circ\text{C}$ to $+125\text{ }^\circ\text{C}$ (IP64)
Operating and storage	$-40\text{ }^\circ\text{C}$ to $+85\text{ }^\circ\text{C}$ (IP68)

Timing diagram

Complementary signals not shown




B leads A for clockwise rotation of magnet.

RM22SC / RM58SC – Absolute binary synchro-serial (SSI), RS422

Serial encoded absolute position measurement

Output code	Natural binary
Power supply	$V_{dd} = 5\text{ V} \pm 5\%$
Current consumption	Max. 35 mA
Data output	Serial data (RS422)
Data input	Clock (RS422)
Accuracy	Typ. $\pm 0.5^\circ$
Hysteresis	0.18°
Resolutions	32, 64, 128, 256, 512, 1,024, 2,048, 4,096 cpr
Maximum speed	60,000 rpm for resolutions up to 1,024 cpr 30,000 rpm for 2,048 and 4,096 cpr
Temperature	$-40\text{ }^\circ\text{C}$ to $+125\text{ }^\circ\text{C}$ (IP64)
Operating and storage	$-40\text{ }^\circ\text{C}$ to $+85\text{ }^\circ\text{C}$ (IP68)

Timing diagram



Clock $\leq 4\text{ MHz}$ $12.5\text{ }\mu\text{s} \leq t_m \leq 20\text{ }\mu\text{s}$
 Position increases for clockwise rotation of magnet.

Part numbering

Encoder system = Encoder body + Magnetic actuator



Encoder body part number
eg **RM22SC0009B10A1B96**

Magnetic actuator
eg **RMA06A2A00**

RM22 SC 00 09B 10 A 1 B 96

Output type

IC - Incremental, RS422

SC - Absolute binary synchro - serial (SSI), RS422

Shaft size

00 - N/A

Resolution

For **IC** and **SC** (counts/positions per revolution):

Binary		
05B - 32	08B - 256	11B - 2048
06B - 64	09B - 512	12B - 4096
07B - 128	10B - 1024	

Cable length

10 - 1 meter (or 10 meters if **0M** special requirement is chosen)

Special requirements

9M - With AM4096 and cable length in meters

96 - With AM4096 - up to 12 bit

Environment and material

B - IP64, Aluminium body (standard)

C - IP68, Aluminium body

J - IP68, Stainless steel body (for Body style 1 only)

Body style and cable exit

1 - Flanged body, radial cable exit

4 - Flanged body, axial cable exit

Connector option

A - 'D' type connector - 9 way

F - Flying lead (no connector)

Magnetic actuator ordering information

Actuator for integration onto shaft



Shaft = \varnothing *h7

Fixing: Grub screw provided

* Hole diameter for nominal shaft size.

Part numbers:

For resolutions of 9 bit absolute (512 cpr incremental)

RMA04A2A00 - 4 mm dia shaft

RMA05A2A00 - 5 mm dia shaft

RMA06A2A00 - 6 mm dia shaft

RMA08A2A00 - 8 mm dia shaft

RMA10A2A00 - 10 mm dia shaft

RMA19A2A00 - 3/16" dia shaft

RMA25A2A00 - 1/4" dia shaft

RMA37A2A00 - 3/8" dia shaft

For resolutions from 10 bit absolute (800 cpr incremental) and above

RMA04A3A00 - 4 mm dia shaft

RMA05A3A00 - 5 mm dia shaft

RMA06A3A00 - 6 mm dia shaft

RMA08A3A00 - 8 mm dia shaft

RMA10A3A00 - 10 mm dia shaft

RMA19A3A00 - 3/16" dia shaft

RMA25A3A00 - 1/4" dia shaft

RMA37A3A00 - 3/8" dia shaft

Head office

RLS merilna tehnika d.o.o.

Poslovna cona Žeje pri Komendi
Pod vrbami 2
SI-1218 Komenda
Slovenia

T +386 1 5272100

F +386 1 5272129

E mail@rls.si

www.rls.si

Document issues

Issue	Date	Page	Corrections made
1	19. 12. 2019	-	New document

This product is not designed or intended for use outside the environmental limitations and operating parameters expressly stated on the product's datasheet. Products are not designed or intended for use in medical, military, aerospace, automotive or oil & gas applications or any safety-critical applications where a failure of the product could cause severe environmental or property damage, personal injury or death. Any use in such applications must be specifically agreed to by seller in writing, and is subject to such additional terms as the seller may impose in its sole discretion. Use of products in such applications is at buyer's own risk, and buyer will indemnify and hold harmless seller and its affiliates against any liability, loss, damage or expense arising from such use. Information contained in this datasheet was derived from product testing under controlled laboratory conditions and data reported thereon is subject to the stated tolerances and variations, or if none are stated, then to tolerances and variations consistent with usual trade practices and testing methods. The product's performance outside of laboratory conditions, including when one or more operating parameters is at its maximum range, may not conform to the product's datasheet. Further, information in the product's datasheet does not reflect the performance of the product in any application, end-use or operating environment buyer or its customer may put the product to. Seller and its affiliates make no recommendation, warranty or representation as to the suitability of the product for buyer's application, use, end-product, process or combination with any other product or as to any results buyer or its customer might obtain in their use of the product. Buyer should use its own knowledge, judgment, expertise and testing in selecting the product for buyer's application, end-use and/or operating environment, and should not rely on any oral or written statement, representation, or samples made by seller or its affiliates for any purpose. EXCEPT FOR THE WARRANTIES EXPRESSLY SET FORTH IN THE SELLER'S TERMS AND CONDITIONS OF SALE, SELLER MAKES NO WARRANTY EXPRESS OR IMPLIED WITH RESPECT TO THE PRODUCT, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE, WHICH ARE DISCLAIMED AND EXCLUDED. All sales are subject to seller's exclusive terms and conditions of sale which, where the seller is (a) RLS merilna tehnika d.o.o., are available at <https://www.rls.si/customer-service>, (b) Renishaw, Inc., are available at <http://www.renishaw.com/Shop/legal/en/-42186>, or (c) another person, are available on request, and in each case, are incorporated herein by reference, and are the exclusive terms of sale. No other terms and conditions apply. Buyer is not authorized to make any statements or representations that expand upon or extend the environmental limitations and operating parameters of the products, or which imply permitted usage outside of that expressly stated on the datasheet or agreed to in writing by seller.

RLS merilna tehnika d.o.o. has made considerable effort to ensure the content of this document is correct at the date of publication but makes no warranties or representations regarding the content. RLS merilna tehnika d.o.o. excludes liability, howsoever arising, for any inaccuracies in this document. © 2019 RLS d.o.o.