


RMB20 angular magnetic encoder module



The RMB20 encoder module provides the functionality of the RM22 encoder in a compact component format for simple customer integration. With a PCB diameter of only 20 mm the module fits into miniature designs.

The encoder module consists of a magnetic actuator and a separate sensor board. Rotation of the magnetic actuator is sensed by a custom encoder chip mounted on the sensor board, and processed to give the required output format. Output signals are provided in industry standard absolute, incremental, analogue, commutation and linear formats.

The RMB20 can be designed into equipment used in a wide range of applications including marine, medical, print, converting, industrial automation, motor control and instrumentation.

Product range

RMB20DC

BiSS C interface with up to 8,192 counts per revolution.

RMB20IC

Incremental with 80 to 2,048 pulses per revolution (320 to 8,192 counts per revolution with x4 evaluation).

RMB20PC

Absolute parallel interface with 512 positions per revolution (9 bit).

RMB20SC


Synchro serial interface (SSI) with 320 to 8,192 positions per revolution.

RMB20Vx

Linear voltage output in a range of variants.


- 20 mm diameter circular module
- 5 V power supply
- High speed operation to 60,000 rpm
- Absolute - to 13 bit resolution (8,192 counts per revolution)
- Industry standard absolute, incremental, commutation and linear voltage output formats
- Accuracy to $\pm 0.5^\circ$

Installation drawing



Module	A PCB surface to magnet distance [mm]	B Chip height [mm]
RMB20 DC	2.50 ± 0.2	Max. 1.00
RMB20 IC	3.50 ± 0.2	Max. 1.60
RMB20 PC		
RMB20 SC		
RMB20 Vx	2.80 ± 0.5	Max. 2

NOTE: For the accuracy specified the center line of the magnet needs to be square to the chip within 2° and aligned within the center of the board ±0.1 mm (mid point between the 2 mounting holes).




Clockwise (CW) rotation of magnet

RMB20DC – Absolute natural binary BiSS C interface


Output code	Natural binary
Power supply	$V_{dd} = 5\text{ V} \pm 5\%$
Current consumption	Max. 50 mA
Clock input	MA (RS422)
Data output	SLO (RS422)
Accuracy	Typ. $\pm 0.5^\circ$
Hysteresis	0.18°
Resolution	320, 400, 500, 512, 800, 1,000, 1,024, 1,600, 2,000, 2,048, 4,096, 8,192 positions per revolution
Maximum speed	30,000 rpm
Operating temperature	-40°C to $+125^\circ\text{C}$ -40°C to $+105^\circ\text{C}$ (with connector)
Max MA frequency	8 MHz

Connections


RMB20DC



RMB20DC with connector



Timing diagram – BiSS C




Data	Length	Description
P24 – P0	0 to 24 bit	Revolution counter value (length depends on the settings chosen)
S12 – S0	3 to 13 bit	Position inside the revolution (length depends on the resolution)
E1 – E0	2 bit	Error data
CRC5 – CRC0	5 to 6 bit	Cyclic redundancy check data; polynomial 0x43; inverted bit output

Error	E0	E1
No error	1	1
Amplitude error	0	1
Too high velocity	1	0
Undervoltage; Configuration; System error	0	0

For more information on BiSS C protocol please visit www.biss-interface.com.

Recommended signal termination

For data output lines only



Connector type

Molex 501568-0607

Mating connector

Molex 501330-0600 (not provided)

Crimp terminal

501334-0000 (not provided)


RMB20IC – Incremental, RS422

Square wave differential line driver to RS422

Power supply	$V_{dd} = 5\text{ V} \pm 5\%$
Current consumption	Max. 35 mA
Output signals	A, B, Z, A–, B–, Z– (RS422)
Accuracy	Typ. $\pm 0.5^\circ$
Hysteresis	0.18°
Resolution	80 to 2,048 pulses per revolution (320, 400, 500, 512, 800, 1,000, 1,024, 1,600, 2,000, 2,048, 4,096, 8,192 counts per revolution)
Maximum speed	30,000 rpm
Temperature	$-40\text{ }^\circ\text{C}$ to $+125\text{ }^\circ\text{C}$
Operating and storage	


Connections

RMB20IC




Timing diagram

Complementary signals not shown



B leads A for clockwise rotation of magnet.

Recommended signal termination




RMB20PC – Absolute binary parallel interface

Parallel absolute position measurement

Output code	Natural binary
Power supply	$V_{dd} = 5\text{ V} \pm 5\%$
Current consumption	20 mA without load
Data outputs	D0 (LSB) - D8 (MSB)
Data input	LE - latch enable input signal, active high Maximum sampling rate 500 kHz
Output voltage	$V_H \geq 4\text{ V}$ at $-I_L \leq 3\text{ mA}$ $V_L \leq 1\text{ V}$ at $I_L \leq 3\text{ mA}$
Accuracy	$\pm 0.7^\circ$
Hysteresis	0.45°
Resolution	9 bit (512 positions per revolution)
Maximum speed	60,000 rpm
Temperature	$-40\text{ }^\circ\text{C}$ to $+125\text{ }^\circ\text{C}$
Operating and storage	


Timing diagram



Position increases for clockwise rotation of magnet.

Connections

RMB20PC




RMB20SC – Absolute binary synchro-serial interface (SSI)

Serial encoded absolute position measurement

Output code	Natural binary
Power supply	$V_{dd} = 5\text{ V} \pm 5\%$
Current consumption	23 mA for 9 bit resolution 35 mA for all other resolutions
Data output	Serial data (RS422)
Data input	Clock (RS422)
Accuracy	Typ. $\pm 0.5^\circ$
Hysteresis	0.18°
Resolution	320, 400, 500, 512, 800, 1,000, 1,024, 1,600, 2,000, 2,048, 4,096, 8,192 positions per revolution
Repeatability	$\leq 0.07^\circ$
Maximum speed	30,000 rpm
Temperature Operating and storage	-40°C to $+125^\circ\text{C}$

Timing diagram




Clock $\leq 4\text{ MHz}$ $12.5\text{ }\mu\text{s} \leq t_m \leq 20.5\text{ }\mu\text{s}$ (for all other resolutions)
 Clock $\leq 900\text{ kHz}$ $16\text{ }\mu\text{s} \leq t_m \leq 22\text{ }\mu\text{s}$ (for 9 bit resolution)

Position increases for clockwise rotation of magnet.


Recommended signal termination

For data output lines only




Connections

RMB20SC - all other resolutions



RMB20SC - 9 bit resolution only




RMB20Vx – Linear voltage output

Power supply	$V_{dd} = 5\text{ V} \pm 5\%$
Current consumption	Typ. 26 mA
Output voltage	0 V to V_{dd}
Output load	Max. 2 mA
Nonlinearity	1 %
Maximum speed	30,000 rpm
Temperature Operating and storage	$-40\text{ }^{\circ}\text{C}$ to $+125\text{ }^{\circ}\text{C}$


Connections

RMB20V




The digital relative angular position information is converted into linear voltage with a built-in 10 bit D/A converter. The linear output voltage swing ranges from 0 V and V_{dd} (5 V). The number of periods within one revolution (N_{period}) can be 1, 2, 4 or 8, representing one full swing over an angle (ϕ_{period}) of 360°, 180°, 90° or 45° respectively. The signal is made up of steps which represent the angular movement needed to register a change in the position (ϕ_{step}) and the resulting change in the output voltage (V_{step}). The number of steps in one period (N_{step}) is given in the table below.

For clockwise rotation of the magnetic actuator, the output voltage increases. For counterclockwise rotation, the output voltage decreases.



Timing diagram for linear voltage output



$$\phi_{\text{step}} = \frac{\phi_{\text{period}}}{N_{\text{step}}} \quad V_{\text{step}} = \frac{V_{dd}}{N_{\text{step}}}$$


- ϕ_{period} = Angle covered in one period (one sawtooth)
- V_{period} = Output voltage range for one period
- ϕ_{step} = Step angle (angular movement needed to register a change in the position)
- V_{step} = Output voltage range for one step
- N_{period} = Number of periods in one revolution
- N_{step} = Number of steps in one period

ϕ_{period}	N_{period}	N_{step}	ϕ_{step}
360°	1	1024	0.35°
180°	2	1024	0.18°
90°	4	1024	0.09°
45°	8	512	0.09°

Output type and electrical variant

ϕ_{period}	360°	180°	90°	45°
Rotation				
Clockwise	VA	VB	VC	VD
Counterclockwise	VE	VF	VG	VH

Part numbering



Decimal			Binary		
D32 - 320	D80 - 800	2D0 - 2000	07B - 128	10B - 1024	13B - 8192
D40 - 400	1D0 - 1000		08B - 256	11B - 2048	
D50 - 500	1D6 - 1600		09B - 512	12B - 4096	

For **PC**:


08B - 256 steps per revolution

For **Vx**:

10B - 1,024 steps per revolution

* For sample quantities of RMB20 supplied with a magnet please add "KIT" to the end of the required RMB20 part number, eg. RMB20IC09BC10KIT.


NOTE: Not all combinations are valid.



Series	Output type	Resolution	Shape	Special requirements
RMB20	DC	2D0 / 1D6 / 1D0 / D80 / D50 / D40 / D32 / 13B / 12B / 11B / 10B / 09B / 08B / 07B	C	10 / C0
	IC			
	SC	2D0 / 1D6 / 1D0 / D80 / D50 / D40 / D32 / 13B / 12B / 11B / 10B / 09B / 08B / 07B		10
	Vx	10B		1

Magnetic actuator and magnet ordering information

Actuator for integration onto shaft



Shaft = Ø*h7

Fixing: Grub screw provided

* Hole diameter for nominal shaft size.
See table on the right for more
information on available shaft sizes.

Part numbers:

For resolutions up to 9 bit absolute (512 cpr incremental)

RMA04A2A00 – Ø4 mm shaft	RMA10A2A00 – Ø10 mm shaft
RMA05A2A00 – Ø5 mm shaft	RMA19A2A00 – Ø3/16" shaft
RMA06A2A00 – Ø6 mm shaft	RMA25A2A00 – Ø1/4" shaft
RMA08A2A00 – Ø8 mm shaft	RMA37A2A00 – Ø3/8" shaft


For resolutions from 10 bit absolute (800 cpr incremental) and above

RMA04A3A00 – Ø4 mm shaft	RMA10A3A00 – Ø10 mm shaft
RMA05A3A00 – Ø5 mm shaft	RMA19A3A00 – Ø3/16" shaft
RMA06A3A00 – Ø6 mm shaft	RMA25A3A00 – Ø1/4" shaft
RMA08A3A00 – Ø8 mm shaft	RMA37A3A00 – Ø3/8" shaft

Actuator for integration into shaft



with N-pole
marker



Part numbers:

For resolutions up to 9 bit absolute (512 cpr incremental)

RMH06A2A00

For resolutions from 10 bit absolute (800 cpr incremental) and above

RMH06A3A00

With N-pole marker scribed to a ±5° accuracy:

For resolutions up to 9 bit absolute (512 cpr incremental)

RMH06A2A02


For resolutions from 10 bit absolute (800 cpr incremental) and above

RMH06A3A02

Hole = Ø6G7

Fixing: Glue (recommended – LOCTITE 648 or 2701)

Magnet for direct recessing in non-ferrous shafts



Fixing: Glue (recommended – LOCTITE 648 or 2701)

Part numbers:

For resolutions up to 9 bit absolute (512 cpr incremental)

RMM44A2A00 (individually packed) – for sample quantities only
RMM44A2C00 (packed in tubes)

For resolutions from 10 bit absolute (800 cpr incremental) and above

RMM44A3A00 (individually packed) – for sample quantities only
RMM44A3C00 (packed in tubes)

Head office

RLS merilna tehnika d.o.o.
Poslovna cona Žeje pri Komendi
Pod vrbami 2
SI-1218 Komenda
Slovenia

T +386 1 5272100

F +386 1 5272129

E mail@rls.si

www.rls.si

Document issues

Issue	Date	Page	Amendments done
10	8. 4. 2016	4, 5	RMB20IC and RMB20SC Connections 9-bit resolution deleted
		6	RMB20Vx description amended
		7	Ordering code amended
11	3. 6. 2016	2, 3	RMB20IC and RMB20SC Connections 9 bit resolution added
12	6. 10. 2016	3	RMB20BC timing diagram and pinout order amended
		4	IC output temperature and Current consumption amended, connections 9 bit resolution deleted
		7	Special requirements option 12 added, resolution binary table amended, ordering table added
13	5. 7. 2018	4, 5	Resolutions amended
14	8. 8. 2019	6	New version of RMB20Vx added
15	30. 8. 2019	2	Dimensions image change
16	27. 9. 2021	2	Dimensions image change
17	2. 2. 2022	General	AC, BC output removed, DC added

This product is not designed or intended for use outside the environmental limitations and operating parameters expressly stated on the product's datasheet. Products are not designed or intended for use in medical, military, aerospace, automotive or oil & gas applications or any safety-critical applications where a failure of the product could cause severe environmental or property damage, personal injury or death. Any use in such applications must be specifically agreed to by seller in writing, and is subject to such additional terms as the seller may impose in its sole discretion. Use of products in such applications is at buyer's own risk, and buyer will indemnify and hold harmless seller and its affiliates against any liability, loss, damage or expense arising from such use. Information contained in this datasheet was derived from product testing under controlled laboratory conditions and data reported thereon is subject to the stated tolerances and variations, or if none are stated, then to tolerances and variations consistent with usual trade practices and testing methods. The product's performance outside of laboratory conditions, including when one or more operating parameters is at its maximum range, may not conform to the product's datasheet. Further, information in the product's datasheet does not reflect the performance of the product in any application, end-use or operating environment buyer or its customer may put the product to. Seller and its affiliates make no recommendation, warranty or representation as to the suitability of the product for buyer's application, use, end-product, process or combination with any other product or as to any results buyer or its customer might obtain in their use of the product. Buyer should use its own knowledge, judgment, expertise and testing in selecting the product for buyer's application, end-use and/or operating environment, and should not rely on any oral or written statement, representation, or samples made by seller or its affiliates for any purpose. EXCEPT FOR THE WARRANTIES EXPRESSLY SET FORTH IN THE SELLER'S TERMS AND CONDITIONS OF SALE, SELLER MAKES NO WARRANTY EXPRESS OR IMPLIED WITH RESPECT TO THE PRODUCT, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE, WHICH ARE DISCLAIMED AND EXCLUDED. All sales are subject to seller's exclusive terms and conditions of sale which, where the seller is (a) RLS merilna tehnika d.o.o., are available at <https://www.rls.si/customer-service>, (b) Renishaw, Inc., are available at <http://www.renishaw.com/Shop/legal/en/-42186>, or (c) another person, are available on request, and in each case, are incorporated herein by reference, and are the exclusive terms of sale. No other terms and conditions apply. Buyer is not authorized to make any statements or representations that expand upon or extend the environmental limitations and operating parameters of the products, or which imply permitted usage outside of that expressly stated on the datasheet or agreed to in writing by seller.

RLS merilna tehnika d.o.o. has made considerable effort to ensure the content of this document is correct at the date of publication but makes no warranties or representations regarding the content. RLS merilna tehnika d.o.o. excludes liability, howsoever arising, for any inaccuracies in this document. © 2022 RLS d.o.o.