

# RE22 rotary magnetic shaft encoder



**The RE22 is a compact, high-speed rotary magnetic encoder designed for use in harsh environments. The traditional design allows for easy integration to existing machines.**

**A magnet is mounted to the shaft within the encoder body. Rotation of this magnet is sensed by a custom encoder chip within the body, and processed to give the required output format.**

The encoder chip processes the signals received to provide resolutions of up to 13 bit (8,192 positions per revolution) with high operational speeds. Output signals are provided in industry standard absolute, incremental, analogue or linear formats.

The compact encoder body is just 22 mm in diameter and provides dirt immunity up to IP53.

The RE22 can be used in a wide range of applications including marine, medical, print, converting, industrial automation, metal working and instrumentation.

## **Product range** **RE22AC**

Analogue with a single sine/cosine cycle per revolution

## **RE22BC**

Complementary analogue outputs with a single sine/cosine cycle per revolution

## **RE22DC**

BiSS C interface with up to 8,192 positions per revolution and optional revolution counter

## **RE22IC**

Incremental with 80 to 2,048 pulses per revolution (320 to 8,192 counts per revolution with x 4 evaluation)

## **RE22SC**


Synchro serial interface (SSI) with 320 to 8,192 positions per revolution

## **RE22Vx**

Linear voltage output in a range of variants



- **High speed operation to 30,000 rpm**
- **Compact - 22 mm diameter body**
- **Absolute - to 13 bit (8,192 ppr)**
- **Industry standard absolute, incremental, analogue and linear output formats**
- **Accuracy to  $\pm 0.3^\circ$**
- **Simple integration**

Storage and handling





**IMPORTANT:** Power to RE22 encoders must be supplied from a DC SELV supply complying with the essential requirements of EN (IEC) 60950 or similar specification.

The RE22 series encoders have been designed to the relevant EMC standards, but must be correctly integrated to achieve EMC compliance. In particular, attention to shielding arrangements is critical.



Connections



D' type connector - 9 way

	RE22AC		RE22BC		RE22DC		RE22IC		RE22SC		RE22V	
Pin nr.	Function	Wire colour	Function	Wire colour	Function	Wire colour	Function	Wire colour	Function	Wire colour	Function	Wire colour
1	Shield - see connection diagram		Shield - see connection diagram		Shield - see connection diagram		Shield - see connection diagram		Shield - see connection diagram		Shield - see connection diagram	
2	V <sub>A</sub>	Green	V <sub>A+</sub>	Green	MA+	White	Z	White	Clock	White	NC	–
3	V <sub>B</sub>	Brown	V <sub>B+</sub>	Brown	MA–	Brown	B	Green	Clock–	Brown	V <sub>out</sub>	Green
4	NC	–	NC	–	NC	–	A	Grey	NC	–	NC	–
5	V <sub>dd</sub>	Red	V <sub>dd</sub>	Red	V <sub>dd</sub>	Red	V <sub>dd</sub>	Red	V <sub>dd</sub>	Red	V <sub>dd</sub>	Red
6	NC	–	V <sub>A–</sub>	Yellow	SLO+	Green	Z–	Brown	Data	Green	NC	–
7	NC	–	V <sub>B–</sub>	White	SLO–	Yellow	B–	Yellow	Data–	Yellow	NC	–
8	NC	–	NC	–	NC	–	A–	Pink	NC	–	NC	–
9	GND	Blue	GND	Blue	GND	Blue	GND	Blue	GND	Blue	GND	Blue

Operating and electrical specifications


EMC compliance	EN 61326
Cable	Outside diameter 5 mm , >R40 static bend radius
Connector options	'D' type connector - 9 way Flying lead
Mass	Encoder unit 1 m cable (no connector) IP53 axial cable 68 g, side cable 60 g.
Environmental sealing	IP53 EN 60529:1992

## Installation drawing


Dimensions and tolerances in mm

### IP53

Axial cable exit



Radial cable exit



### Special option 06

Flat, D-shaped shaft




Table of expected bearing life ratings in hours

Speed (rpm)	Rad. load 5 N	Rad. load 10 N	Rad. load 15 N	Rad. load 20 N
500	205,401	98,455	54,569	33,333
1,000	102,700	49,227	27,285	16,667
2,000	51,350	24,613	13,642	8,333
5,000	20,540	9,845	5,457	3,333
10,000	10,270	4,923	2,728	1,667
15,000	6,847	3,282	1,819	1,111
30,000	5,135	2,461	1,364	833


Maximum recommended shaft loads: radial 20N, axial 10N

## RE22AC – Analogue sinusoidal outputs

2 channels  $V_A$   $V_B$  sinusoids (90° phase shifted, single ended)

<b>Power supply</b>	$V_{dd} = 5\text{ V} \pm 5\%$
<b>Power consumption</b>	30 mA
<b>Outputs</b>	Single ended Signal amplitude $2.2 \pm 0.2\text{ V}_{pp}$ Signal offset (Vref) $2.5\text{ V} \pm 1\%$
<b>Internal serial impedance</b>	10 $\Omega$
<b>Maximum speed</b>	30,000 rpm
<b>Maximum cable length</b>	3 m
<b>Operating temperature</b>	-40 °C to +120 °C

Timing diagram




$V_A$  leads  $V_B$  by 90° for clockwise rotation of magnetic actuator.

## RE22BC – Analogue complementary sinusoidal outputs

2 channels  $V_A$  and  $V_B$  differential sinusoids in quadrature (90° phase shifted)

<b>Power supply</b>	$V_{dd} = 5\text{ V} \pm 5\%$
<b>Power consumption</b>	30 mA
<b>Outputs</b>	Differential Signal amplitude $0.5 \pm 0.1\text{ V}_{pp}$ Signal offset (Vref) $0 \pm 5\text{ mV}$
<b>Internal serial impedance</b>	10 $\Omega$
<b>Maximum speed</b>	30,000 rpm
<b>Maximum cable length</b>	20 m
<b>Operating temperature</b>	-40 °C to +120 °C

Timing diagram




$V_A$  leads  $V_B$  by 90° for clockwise rotation of magnetic actuator.

## RE22DC – Absolute natural binary BiSS C interface

<b>Output code</b>	Natural binary
<b>Power supply</b>	$V_{dd} = 5\text{ V} \pm 5\%$
<b>Current consumption</b>	Max. 50 mA
<b>Clock input</b>	MA (RS422)
<b>Data output</b>	SLO (RS422)
<b>Accuracy</b>	Typ. $\pm 0.5^\circ$
<b>Hysteresis</b>	$0.18^\circ$
<b>Resolution</b>	320, 400, 500, 512, 800, 1,000, 1,024, 1,600, 2,000, 2,048, 4,096, 8,192 positions per revolution
<b>Revolution counter</b>	12 bit (4096 revolutions)
<b>Maximum speed</b>	30,000 rpm
<b>Operating temperature</b>	$-40^\circ\text{C}$ to $+120^\circ\text{C}$
<b>Max MA frequency</b>	8 MHz

### Timing diagram – BiSS C



Data	Length	Description
P11 – P0	0 or 12 bit	Revolution counter value when enabled (see Part numbering/ resolution)*
S12 – S0	7 to 13 bit	Position inside the revolution (length depends on the resolution)
E1 – E0	2 bit	Error data
CRC5 – CRC0	5 to 6 bit	Cyclic redundancy check data; polynomial 0x43; inverted bit output


Error	E0	E1
No error	1	1
Amplitude error	0	1
Too high velocity	1	0
Undervoltage; Configuration; System error	0	0

\* The revolution counter counts the number of mechanical revolutions of the shaft or magnet of the encoder. Counting is possible only when the encoder is powered. When the encoder is powered off, the revolution counter is reset to 0.

For more information on BiSS C protocol please visit [www.biss-interface.com](http://www.biss-interface.com).

### Recommended signal termination

For data output lines only




## RE22IC – Incremental outputs

Square wave differential line driver to RS422


<b>Power supply</b>	$V_{dd} = 5\text{ V} \pm 5\%$
<b>Power consumption</b>	Max. 35 mA
<b>Output signals</b>	A, B, Z, A–, B–, Z– (RS422)
<b>Accuracy</b>	Typ. $\pm 0.5^\circ$
<b>Hysteresis</b>	$0.18^\circ$
<b>Resolution</b>	80 to 2,048 pulses per revolution (320, 400, 500, 512, 800, 1,000, 1,024, 1,600, 2,000, 2,048, 4,096, 8,192 counts per revolution)
<b>Maximum speed</b>	30,000 rpm
<b>Maximum cable length</b>	50 m
<b>Operating temperature</b>	$-40^\circ\text{C}$ to $+120^\circ\text{C}$

### Timing diagram

Complementary signals not shown



### Recommended signal termination




## RE22SC – Absolute binary synchro-serial interface (SSI)

Serial encoded absolute position measurement


<b>Output code</b>	Natural binary
<b>Power supply</b>	$V_{dd} = 5\text{ V} \pm 5\%$
<b>Power consumption</b>	Max. 35 mA
<b>Data output</b>	Serial data (RS422)
<b>Data input</b>	Clock (RS422)
<b>Accuracy</b>	Typ. $\pm 0.5^\circ$
<b>Hysteresis</b>	$0.18^\circ$
<b>Resolution</b>	320, 400, 500, 512, 800, 1,000, 1,024, 1,600, 2,000, 2,048, 4,096, 8,192 positions per revolution
<b>Maximum speed</b>	30,000 rpm
<b>Maximum cable length</b>	100 m (at 1 MHz)
<b>Operating temperature</b>	$-40^\circ\text{C}$ to $+120^\circ\text{C}$

### Timing diagram



### Recommended signal termination

For data output lines only



## RE22Vx – Linear voltage output


Power supply	$V_{dd} = 5\text{ V} \pm 5\%$
Power consumption	Typ. 26 mA
Output voltage	0 V to $V_{dd}$
Output loading	Max. 10 mA
Nonlinearity	1 %
Maximum speed	30,000 rpm
Maximum cable length	20 m
Operating temperature	-40 °C to +120 °C

$\Phi_{\text{period}}$	$N_{\text{period}}$	$N_{\text{step}}$	$\Phi_{\text{step}}$
360°	1	1,024	0.35°
180°	2	1,024	0.18°
90°	4	1,024	0.09°
45°	8	512	0.09°

## Output type and electrical variant

Rotation \ $\Phi_{\text{period}}$	360°	180°	90°	45°
Clockwise	VA	VB	VC	VD
Counterclockwise	VE	VF	VG	VH

## Timing diagram



$$\Phi_{\text{step}} = \frac{\Phi_{\text{period}}}{N_{\text{step}}} \quad V_{\text{step}} = \frac{V_{dd}}{N_{\text{step}}}$$

- $\Phi_{\text{period}}$  = Angle covered in one period (one sawtooth)
- $V_{\text{period}}$  = Output voltage range for one period
- $\Phi_{\text{step}}$  = Step angle (angular movement needed to register a change in the position)
- $V_{\text{step}}$  = Output voltage range for one step
- $N_{\text{period}}$  = Number of periods in one revolution
- $N_{\text{step}}$  = Number of steps in one period

Data sheet  
**RE22D01\_10**

**Part numbering**



Encoder part number  
eg **RE22SC0409B10A3A00**

**RE22 SC 04 09B 10 A 3 A 00**

**Output type**

**AC** - Analogue sinusoidal 2 V<sub>pp</sub>  
**BC** - Analogue complementary sinusoidal  
**DC** - Absolute natural binary BiSS C, RS422  
**IC** - Incremental, RS422  
**SC** - Absolute binary synchro-serial (SSI), RS422  
**Vx** - Linear voltage:

Linear voltage output 0 - 5 V, supply 5 V DC				
	360°	180°	90°	45°
CW	<b>VA</b>	<b>VB</b>	<b>VC</b>	<b>VD</b>
CCW	<b>VE</b>	<b>VF</b>	<b>VG</b>	<b>VH</b>

**Shaft size**

**04** - 4 mm

**Resolution**

For output types **AC** and **BC**:

**01S** - One sine/cosine wave per revolution

For output type **Vx**:

**10B** - 1,024 positions per revolution

For output types **DC**, **IC** and **SC** (counts or positions per revolution):

Decimal			Binary	
<b>D32</b> - 320	<b>D80</b> - 800	<b>2D0</b> - 2000	<b>09B</b> - 512	<b>12B</b> - 4096
<b>D40</b> - 400	<b>1D0</b> - 1000		<b>10B</b> - 1024	<b>13B</b> - 8192
<b>D50</b> - 500	<b>1D6</b> - 1600		<b>11B</b> - 2048	

For output types **DC** with enabled 12 bit revolution counter:

Decimal			Binary	
<b>M32</b> - 320	<b>M80</b> - 800	<b>2M0</b> - 2000	<b>09M</b> - 512	<b>12M</b> - 4096
<b>M40</b> - 400	<b>1M0</b> - 1000		<b>10M</b> - 1024	<b>13M</b> - 8192
<b>M50</b> - 500	<b>1M6</b> - 1600		<b>11M</b> - 2048	

**Special requirements**

**00** - None  
**06** - With flat, D-shaped shaft  
**0M** - Cable length in meters

**Environment and material**

**A** - IP53, aluminium body (standard)

**Body style and cable exit**

**2** - Cylindrical body, radial cable exit  
**3** - Cylindrical body, axial cable exit

**Connector option**

**A** - 'D' type connector - 9 way  
**F** - Flying lead (no connector)

**Cable length**

**10** - 1.0 meter (10 meters if **0M** is chosen)

**NOTE:** Not all combinations are valid.

Series	Output type	Shaft size	Resolution	Cable length	Connector option	Body style and cable exit	Environment	Special requirements	
RE22	AC	04	01S	10	A / F	2 / 3	A	00 / 06 / 0M	
	BC								
	DC		09B / D50 / D40 / D32 / 10B / 1D0 / D80 / 11B / 2D0 / 1D6 /12B / 13B 09M / M50 / M40 / M32 / 10M / 1M0 / M80 / 11M / 2M0 / 1M6 /12M / 13M						
			IC						09B / D50 / D40 / D32 / 10B / 1D0 / D80 / 11B / 2D0 / 1D6 /12B / 13B
									SC
	Vx		10B						

## Head office

**RLS Merilna tehnika d. o. o.**  
Poslovna cona Žeje pri Komendi  
Pod vrbami 2  
SI-1218 Komenda  
Slovenia

**T** +386 1 5272100

**E** mail@rls.si

**www.rls.si**

## Document issues

Issue	Date	Page	Corrections made
1	13. 1. 2011	-	New document
2	9. 7. 2015	2	Storage and handling info added; connections diagram and table added
		3	Installation drawing tolerances updated, flat D-shaped shaft drawing added
		4-6	Temperature range amended
		6	Parallel output removed
		7	Parallel output removed, resolution options updated and special option 06 added
3	18. 5. 2018	5	Resolutions amended
4	4. 7. 2018	General	Resolutions amended
5	28. 2. 2019	3	IP64/68 radial cable exit drawing removed
6	2. 10. 2019	1	Speed changed
7	2. 2. 2022	General	DC output added
8	19. 5. 2022	2	DC output wire color amended, cable data amended
		General	IP64/IP68 deleted
9	19. 1. 2023	4	BC output temperature amended, revolution counter added
10	12. 9. 2023	5	DC output temperature amended

This product is not designed or intended for use outside the environmental limitations and operating parameters expressly stated on the product's datasheet. Products are not designed or intended for use in medical, military, aerospace, automotive or oil & gas applications or any safety-critical applications where a failure of the product could cause severe environmental or property damage, personal injury or death. Any use in such applications must be specifically agreed to by seller in writing, and is subject to such additional terms as the seller may impose in its sole discretion. Use of products in such applications is at buyer's own risk, and buyer will indemnify and hold harmless seller and its affiliates against any liability, loss, damage or expense arising from such use. Information contained in this datasheet was derived from product testing under controlled laboratory conditions and data reported thereon is subject to the stated tolerances and variations, or if none are stated, then to tolerances and variations consistent with usual trade practices and testing methods. The product's performance outside of laboratory conditions, including when one or more operating parameters is at its maximum range, may not conform to the product's datasheet. Further, information in the product's datasheet does not reflect the performance of the product in any application, end-use or operating environment buyer or its customer may put the product to. Seller and its affiliates make no recommendation, warranty or representation as to the suitability of the product for buyer's application, use, end-product, process or combination with any other product or as to any results buyer or its customer might obtain in their use of the product. Buyer should use its own knowledge, judgment, expertise and testing in selecting the product for buyer's application, end-use and/or operating environment, and should not rely on any oral or written statement, representation, or samples made by seller or its affiliates for any purpose. EXCEPT FOR THE WARRANTIES EXPRESSLY SET FORTH IN THE SELLER'S TERMS AND CONDITIONS OF SALE, SELLER MAKES NO WARRANTY EXPRESS OR IMPLIED WITH RESPECT TO THE PRODUCT, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE, WHICH ARE DISCLAIMED AND EXCLUDED. All sales are subject to seller's exclusive terms and conditions of sale which, where the seller is (a) RLS Merilna tehnika d. o. o., are available at <https://www.rls.si/customer-service>, (b) Renishaw, Inc., are available at <http://www.renishaw.com/Shop/legal/en/-42186>, or (c) another person, are available on request, and in each case, are incorporated herein by reference, and are the exclusive terms of sale. No other terms and conditions apply. Buyer is not authorized to make any statements or representations that expand upon or extend the environmental limitations and operating parameters of the products, or which imply permitted usage outside of that expressly stated on the datasheet or agreed to in writing by seller.

RLS Merilna tehnika d. o. o. has made considerable effort to ensure the content of this document is correct at the date of publication but makes no warranties or representations regarding the content. RLS Merilna tehnika d. o. o. excludes liability, howsoever arising, for any inaccuracies in this document. © 2023 RLS d. o. o.