


RMB28 angular magnetic encoder module



The image does not represent all variants.

The RMB28 encoder module is designed for direct integration to high volume OEM applications. The low cost 28 mm square PCB can also be provided with a connector for easy installation.

The encoder module consists of a magnetic actuator and a separate sensor board. Rotation of the magnetic actuator is sensed by a custom encoder chip mounted on the sensor board, and processed to give the required output format. Output signals are provided in industry standard absolute, incremental, analogue or linear formats.

The RMB28 can be used in a wide range of OEM applications including motor control and industrial automation.

RMB28MD - Sine/Cosine + Absolute binary synchro-serial + Incremental, 5 V

RMB28IB - Incremental, Open Collector, 24 V

RMB28IE - Incremental, Open Collector, 5 V

RMB28IC - Incremental, RS422, 5 V


RMB28SC - Absolute binary synchro-serial, RS422, 5 V

RMB28SI - Absolute binary synchro-serial (SSI) + Incremental, RS422, 5 V

RMB28V - Linear voltage output, 5 V

- 28 mm square module
- Low cost for OEM integration
- 24 V and 5 V power supply versions
- High speed operation to 60,000 rpm
- Absolute - to 13 bit resolution (8,192 counts per revolution)
- Industry standard absolute, incremental, analogue and linear output formats
- Accuracy to $\pm 0.5^\circ$
- RoHS compliant (lead free)

RMB28 installation drawing



Output type	Hole diameter (D)
RMB28MD	3.5 ±0.1
RMB28IB	3.5 ±0.1
RMB28IE	3.5 ±0.1
RMB28IC - 128, 256 cpr	3.5 ±0.1
RMB28IC - all other resolutions	2.5 ±0.1
RMB28SC - 8 bit	3.5 ±0.1
RMB28SC - all other resolutions	2.5 ±0.1
RMB28SI	2.5 ±0.1
RMB28V	3.5 ±0.1



Clockwise (CW) rotation of magnet

RMB28MD – Sine/Cosine + Absolute binary synchro-serial (SSI) + Incremental


Complex feedback device for absolute position at start-up as well as during operation + incremental outputs

Power supply	$V_{dd} = 5 \text{ V} \pm 5\%$
Resolution	8 bit + 64 ppr (256 cpr) + one period per revolution
Power consumption	13 mA – incremental and SSI (not loaded)
SSI output code	Natural binary
Data output	Serial data
Data input	Clock
Incremental outputs	A, B, Z
Sin/Cos outputs	Signal amplitude $2 \pm 0.2 \text{ V}_{pp}$ Signal offset $V_{dd}/2 \pm 5 \text{ mV}$
Operating temperature	-40 °C to +125 °C
Maximum speed	60,000 rpm
Accuracy*	$\pm 0.7^\circ$
Hysteresis	0.45°


* Worst case within operational parameters including magnet position and temperature.

Connections

RMB28MD




Timing diagram - SSI




Position increases for clockwise rotation of magnet.

Timing diagram - Incremental



B leads A for clockwise rotation of magnet.

Timing diagram - Sine/Cosine



V_B leads V_A for clockwise rotation of magnet.

Data sheet
RMB28D01_07

RMB28IB – Incremental, Open Collector, NPN, 24 V


Square wave output

Power supply	$V_{dd} = 8 \text{ V to } 26 \text{ V}$
Resolution	32, 64 ppr (128, 256 cpr)
Power consumption	13 mA (not loaded)
Maximum output load	20 mA
Output signals	A, B, Z
Operating temperature	0 °C to +70 °C Ext. operat. temp. -40 °C to +125 °C
Maximum speed	60,000 rpm
Accuracy*	±0.7°
Hysteresis	0.45°


* Worst case within operational parameters including magnet position and temperature.

Connections

RMB28IB




Timing diagram



B leads A for clockwise rotation of magnet.

Recommended signal termination



RMB28IE – Incremental, Open Collector, NPN, 5 V

Low cost alternative for ball bearing encoders

Power supply	$V_{dd} = 5 \text{ V} \pm 5\%$
Power consumption	13 mA for 128, 256 cpr 35 mA for all other resolutions
Maximum output load	20 mA
Output signals	A, B, Z
Operating temperature	0 °C to +70 °C Ext. operat. temp. -40 °C to +125 °C


* Worst case within operational parameters including magnet position and temperature.

Resolution options (counts per revolution)	Maximum speed (rpm)	Accuracy*	Hysteresis
128, 256	60,000	±0.7°	0.45°
320, 400, 500, 512	30,000	±0.7°	0.18°
800, 1,000, 1,024	20,000	±0.5°	0.18°
1,600, 2,000, 2,048	10,000	±0.5°	0.18°
4,096	5,000	±0.5°	0.18°
8,192	2,500	±0.5°	0.18°


* Worst case within operational parameters including magnet position and temperature.

Connections

RMB28IE - 32, 64 pulses per revolution (128, 256 cpr)




Timing diagram




B leads A for clockwise rotation of magnet.

Recommended signal termination



RMB28IE - all other resolutions



Data sheet
RMB28D01_07

RMB28IC – Incremental, RS422, 5 V

Alternative for optical encoders


Power supply	$V_{dd} = 5 \text{ V} \pm 5\%$
Power consumption	13 mA for 128, 256 cpr 35 mA for all other resolutions
Output signals	A, B, Z, A-, B-, Z- (RS422)
Operating temperature	-25 °C to +85 °C Ext. operat. temp. -40 °C to +125 °C
Edge separation	1 μs minimum

Resolution options (counts per revolution)	Maximum speed (rpm)	Accuracy*	Hysteresis
128, 256	60,000	$\pm 0.7^\circ$	0.45°
320, 400, 500, 512	30,000	$\pm 0.7^\circ$	0.18°
800, 1,000, 1,024	20,000	$\pm 0.5^\circ$	0.18°
1,600, 2,000, 2,048	10,000	$\pm 0.5^\circ$	0.18°
4,096	5,000	$\pm 0.5^\circ$	0.18°
8,192	2,500	$\pm 0.5^\circ$	0.18°

* Worst case within operational parameters including magnet position and temperature.


Connections

RMB28IC - 128, 256 counts per revolution




Timing diagram


Complementary signals not shown



Recommended signal termination



RMB28IC - all other resolutions



RMB28SC – Absolute binary synchro-serial (SSI), RS422, 5 V

Alternative for optical encoders


Power supply	$V_{dd} = 5 \text{ V} \pm 5\%$
Power consumption	13 mA for 8 bit resolution 35 mA for all other resolutions
SSI output code	Natural binary
Data output	Serial data (RS422)
Data input	Clock (RS422)
Operating temperature	-40 °C to +125 °C
Maximum speed	60,000 rpm

Resolution options (positions per rev)	Maximum speed (rpm)	Accuracy*	Hysteresis
256	60,000	±0.7	0.45°
320, 400, 500, 512	30,000	±0.7°	0.18°
800, 1,000, 1,024	20,000	±0.5°	0.18°
1,600, 2,000, 2,048	10,000	±0.5°	0.18°
4,096	5,000	±0.5°	0.18°
8,192	2,500	±0.5°	0.18°


* Worst case within operational parameters including magnet position and temperature.

Connections

RMB28SC - 8 bit resolution



Timing diagram




Clock ≤ 900 kHz 16 µs ≤ t_m ≤ 22 µs for 8 bit resolution

Clock ≤ 4 MHz 12.5 µs ≤ t_m ≤ 20 µs for all other resolutions


Position increases for clockwise rotation of magnet.

Recommended signal termination

For data output lines only



RMB28SC - all other resolutions



Data sheet
RMB28D01_07

RMB28SI – Absolute binary synchro-serial (SSI) + Incremental, RS422, 5 V

Complex feedback device for absolute position at start up as well as during operation + incremental outputs.
Both the incremental and the SSI output always have the same fixed resolution.


Power supply	$V_{dd} = 5 \text{ V} \pm 5\%$
Power consumption	35 mA
SSI output code	Natural binary
Data output	Serial data (RS422)
Data input	Clock (RS422)
Incremental outputs	A, B, Z, A-, B-, Z- (RS422)
Operating temperature	-25 °C to +85 °C Ext. operat. temp. -40 °C to +125 °C

Resolution options (positions/counts per revolution)	Maximum speed (rpm)	Accuracy*	Hysteresis
320, 400, 500, 512	30,000	±0.7°	0.18°
800, 1,000, 1,024	20,000	±0.5°	0.18°
1,600, 2,000, 2,048	10,000	±0.5°	0.18°
4,096	5,000	±0.5°	0.18°
8,192	2,500	±0.5°	0.18°

* Worst case within operational parameters including magnet position and temperature.

Connections

RMB28SI




RMB28V – Linear voltage output

Alternative for potentiometers


Power supply	$V_{dd} = 5 \text{ V} \pm 5\%$
Power consumption	20 mA (not loaded)
Output voltage	0 V to V_{dd}
Output loading	Max. 10 mA
Nonlinearity	1 %
Operating temperature	-40 °C to +125 °C
Maximum speed	30,000 rpm

Connections

RMB28V




Timing diagram - SSI



Clock ≤ 4 MHz $12.5 \mu\text{s} \leq t_m \leq 20.5 \mu\text{s}$
Position increases for clockwise rotation of magnetic actuator.

Timing diagram - Incremental


Complementary signals not shown




B leads **A** for clockwise rotation of magnetic actuator.

Recommended signal termination

For incremental signals + SSI data output lines only




Electrical output



Output type and electrical variant

ϕ_{FS}	360°	180°	90°	45°
CW	VA	VB	VC	VD
CCW	VE	VF	VG	VH

RMB28 ordering code



NOTE: Not all combinations are valid.

For output types **IC, IE, SC and SI**:

Decimal			Binary		
D32 - 320	D80 - 800	2D0 - 2000	07B - 128*	10B - 1024	13B - 8192
D40 - 400	1D0 - 1000		08B - 256**	11B - 2048	
D50 - 500	1D6 - 1600		09B - 512	12B - 4096	


* For **IC** and **IE** output types only.

** For output types **IC, IE** and **SC**.



NOTE: For sample quantities of RMB28 supplied with a magnet please add "KIT" to the end of the required RMB28 part number, eg. RMB28IC09BS10KIT

Connector options (for output types **IC, SC** and **SI** only)



The layout of the pads on the board is suitable for the MOLEX 43045-1219 connector (mating part MOLEX 43025-1200 + crimp terminal 43030-xxxx).


Data sheet
RMB28D01_07

Magnetic actuator and magnet ordering information

Actuator for integration onto shaft



Shaft = Ø*h7
Fixing: Grub screw provided




Part numbers:

For resolutions up to 9 bit absolute (512 cpr incremental)
RMA04A2A00 – Ø4 mm shaft **RMA10A2A00** – Ø10 mm shaft
RMA05A2A00 – Ø5 mm shaft **RMA19A2A00** – Ø3/16" shaft
RMA06A2A00 – Ø6 mm shaft **RMA25A2A00** – Ø1/4" shaft
RMA08A2A00 – Ø8 mm shaft **RMA37A2A00** – Ø3/8" shaft

For resolutions from 10 bit absolute (800 cpr incremental) and above
RMA04A3A00 – Ø4 mm shaft **RMA10A3A00** – Ø10 mm shaft
RMA05A3A00 – Ø5 mm shaft **RMA19A3A00** – Ø3/16" shaft
RMA06A3A00 – Ø6 mm shaft **RMA25A3A00** – Ø1/4" shaft
RMA08A3A00 – Ø8 mm shaft **RMA37A3A00** – Ø3/8" shaft

Actuator for integration into shaft



Part numbers:

For resolutions up to 9 bit absolute (512 cpr incremental)
RMH06A2A00

For resolutions from 10 bit absolute (800 cpr incremental) and above
RMH06A3A00

With N-pole marker scribed to a ± 5° accuracy:


For resolutions up to 9 bit absolute (512 cpr incremental)
RMH06A2A02

For resolutions from 10 bit absolute (800 cpr incremental) and above
RMH06A3A02

Hole = Ø6G7

Fixing: Glue (recommended – LOCTITE 648)

Magnet for direct recessing in non-ferrous shafts



Fixing: Glue (recommended – LOCTITE 648)

Part numbers:

For resolutions up to 9 bit absolute (512 cpr incremental)
RMM44A2A00 (individually packed) – for sample quantities only
RMM44A2C00 (packed in tubes)

For resolutions from 10 bit absolute (800 cpr incremental) and above
RMM44A3A00 (individually packed) – for sample quantities only
RMM44A3C00 (packed in tubes)

Head office

RLS merilna tehnika d.o.o.

Poslovna cona Žeje pri Komendi
Pod vrbami 2
SI-1218 Komenda
Slovenia

T +386 1 5272100
F +386 1 5272129
E mail@rls.si
www.rls.si

Document issues

Issue	Date	Page	Amendments done
01	5. 12. 2006	-	New document
02	1. 2. 2008	-	New layout with outputs IB and V _x , minor amendments
03	25. 11. 2008	2	Power consumption for IB output type changed to 13 mA
		-	New connection images with high resolution data added
04	14. 1. 2009	-	New layout
05	10. 2. 2010	2	Hole diameter table added
06	17.11.2010	-	Extended operating temperature range description changed
07	14. 5. 2014	5	RMB28IE high resolution version added

Australia
T +61 3 9521 0922
E australia@renishaw.com

Austria
T +43 2236 379790
E austria@renishaw.com

Brazil
T +55 11 4195 2866
E brazil@renishaw.com

Canada
T +1 905 828 0104
E canada@renishaw.com

The People's Republic of China
T +86 20 8550 9485
E guangzhou@renishaw.com

Czech Republic
T +420 5 4821 6553
E czech@renishaw.com

France
T +33 1 64 61 84 84
E france@renishaw.com

Germany
T +49 7127 9810
E verkauf@renishaw.com

Hong Kong
T +852 2753 0638
E hongkong@renishaw.com

Hungary
T +36 23 502 183
E hungary@renishaw.com

India
T +91 20 6674 6200
E india@renishaw.com

Italy
T +39 011 966 10 52
E italy@renishaw.com

Japan
T +81 3 5366 5316
E japan@renishaw.com

The Netherlands
T +31 76 543 11 00
E benelux@renishaw.com

Poland
T +48 22 577 11 80
E poland@renishaw.com

Russia
T +7 495 231 1677
E russia@renishaw.com

Singapore
T +65 6897 5466
E singapore@renishaw.com

South Korea
T +82 2 2108 2830
E korea@renishaw.com

Spain
T +34 93 663 34 20
E spain@renishaw.com

Sweden
T +46 8 584 90 880
E sweden@renishaw.com

Switzerland
T +41 55 415 50 60
E switzerland@renishaw.com

Taiwan
T +886 4 2473 3177
E taiwan@renishaw.com

Turkey
T +90 216 380 92 40
E turkiye@renishaw.com

UK
T +44 1453 524524
E uk@renishaw.com

USA
T +1 847 286 9953
E usa@renishaw.com

**For all other countries
please contact RLS' head
office**