


RMB30 angular magnetic encoder module



The image does not represent all variants.

The RMB30 encoder module offers the functionality of the RM36 encoder in a component format for easy customer integration. With a wide range of outputs and both 5 V and 24 V power supply variants the device can be easily integrated into existing electronics.

The encoder module consists of a magnetic actuator and a separate sensor board. The rotation of the magnetic actuator is sensed by a custom encoder chip mounted on the sensor board, and processed to produce the required output format. The output signals are provided in industry standard absolute, incremental, analogue or linear formats.

The RMB30 can be used in a variety of applications including marine, medical, printing, processing, industrial automation, metalworking, engine control and instrumentation.

Product range

RMB30Cx

Linear current output in a range of variants.

RMB30IA

Incremental output, Push-Pull, 24 V

RMB30IB

Incremental output, Open Collector NPN, 24 V

RMB30IC

Incremental with up to 2,048 pulses per revolution (up to 8,192 counts per revolution with x4 evaluation).

RMB30SC

Synchro serial interface (SSI) with up to 8,192 positions per revolution.

RMB30SI


Synchro serial interface (SSI) and incremental outputs.

RMB30Vx

Linear voltage output in a range of variants.


- 30 mm diameter circular module
- 24 V and 5 V power supply versions
- High speed operation to 30,000 rpm
- Absolute - to 13 bit resolution (8,192 counts per revolution)
- Industry standard absolute, incremental, analogue and linear output formats
- Accuracy to $\pm 0.5^\circ$
- RoHS compliant (lead free) - see Declaration of conformity

Installation drawing



Module	D
IA, IB, IC	3.5 ± 0.2
SC, SI	3.5 ± 0.2
Cx, Vx	2.8 ± 0.5

NOTE: For the accuracy specified the center line of the magnet needs to be square to the chip within 2° and aligned within the center of the board ± 0.1 mm (mid point between the 2 mounting holes).




Clockwise (CW) rotation of magnet

RMB301A – Incremental, Push-pull

Square wave output


Power supply	$V_{dd} = 8\text{ V to }26\text{ V}$
Current consumption	Typ. 40 mA
Output signals	A, B, Z, A–, B–, Z– (RS422)
Maximum output load	30 mA
Accuracy	Typ. $\pm 0.5^\circ$
Hysteresis	0.18°
Resolution	80 to 2,048 pulses per revolution (up to 8,192 counts per revolution)
Maximum speed	30,000 rpm
Temperature	$-40\text{ }^\circ\text{C to }+125\text{ }^\circ\text{C}$
Operating and storage	

Connections



Timing diagram

Complementary signals not shown




B leads A for clockwise rotation of magnet.

RMB30IB – Incremental, Open Collector, NPN

Square wave output


Power supply	$V_{dd} = 8\text{ V to }26\text{ V}$
Current consumption	Typ. 40 mA
Output signals	A, B, Z
Maximum output load	20 mA
Accuracy	Typ. $\pm 0.5^\circ$
Hysteresis	0.18°
Resolution	80 to 2,048 pulses per revolution (up to 8,192 counts per revolution)
Maximum speed	30,000 rpm
Temperature	$-40^\circ\text{C to }+125^\circ\text{C}$
Operating and storage	

Timing diagram




B leads A for clockwise rotation of magnet.

Connections



Recommended signal termination




NOTE 1: RMB30IA and RMB30IB boards need 2 power supplies; pad V_{dd} needs 24 V and pad +5 V needs 5 V. Pads V_{in} , GND and +5 V have been provided to allow easy connection to a 3 terminal voltage regulator to generate 5 V from 24 V.

RMB30IC – Incremental outputs

Square wave differential line driver to RS422

Power supply	$V_{dd} = 5\text{ V} \pm 5\%$
Current consumption	Typ. 40 mA
Output signals	A, B, Z, A-, B-, Z- (RS422)
Accuracy	Typ. $\pm 0.5^\circ$
Hysteresis	0.18°
Resolution	80 to 2,048 pulses per revolution (up to 8,192 counts per revolution)
Maximum speed	30,000 rpm
Temperature	-40°C to $+125^\circ\text{C}$
Operating and storage	


Connections



A-
A
Z
Z-
B-
B
GND
V_{dd}


Timing diagram

Complementary signals not shown



B leads A for clockwise rotation of magnet.

Recommended signal termination




RMB30SC – Absolute binary synchro-serial interface (SSI)


Serial encoded absolute position measurement

Output code	Natural binary
Power supply	$V_{dd} = 5\text{ V} \pm 5\%$
Current consumption	Typ. 40 mA
Data output	Serial data (RS422)
Data input	Clock (RS422)
Accuracy	Typ. $\pm 0.5^\circ$
Hysteresis	0.18°
Resolution	up to 8,192 counts per revolution
Maximum speed	30,000 rpm
Temperature Operating and storage	$-40\text{ }^\circ\text{C}$ to $+125\text{ }^\circ\text{C}$


Connections



Timing diagram



Recommended signal termination




RMB30SI – Absolute binary synchro-serial (SSI) + Incremental, RS422

Complex feedback device for absolute position at start up as well as during operation + incremental outputs.
Both the incremental and the SSI output always have the same fixed resolution.

Output code	Natural binary
Power supply	$V_{dd} = 5\text{ V} \pm 5\%$
Current consumption	Typ. 40 mA
Incremental outputs	A, B, Z, A-, B-, Z- (RS422)
Data output	Serial data (RS422)
Data input	Clock (RS422)
Accuracy	Typ. $\pm 0.5^\circ$
Hysteresis	0.18°
Resolution	80 to 2,048 pulses per revolution (up to 8,192 counts per revolution)
Maximum speed	30,000 rpm
Temperature	-40°C to $+125^\circ\text{C}$
Operating and storage	


Connections



A-
A
Z
Z-
B-
B
Data-
Data
Clock-
Clock
GND
V_{dd}

Timing diagram - SSI


Complementary signals not shown



Position increases for clockwise rotation of magnet.


Timing diagram - incremental

Complementary signals not shown



B leads A for clockwise rotation of magnet.

Recommended signal termination




RMB30Cx – Linear current output

Power supply	$V_{dd} = 20\text{ V to }30\text{ V DC}$ Reverse polarity protection
Current consumption	50 mA plus output current
Output current	4 mA to 20 mA
Output loading	$R_L = 0$ to $\frac{V_{dd}}{I_{OUTmax}}$
Nonlinearity	1 %
Maximum speed	30,000 rpm
Temperature	-25 °C to +85 °C
Operating and storage	


Output type and electrical variant

φ_{FS}	360°	180°	90°	45°
Clockwise	CA	CB	CC	CD
Counterclockwise	CE	CF	CG	CH

Electrical output/shaft position



Connections



RMB30Vx / RMF44Vx – Linear voltage output


Alternative for potentiometers

Power supply	$V_{dd} = 20\text{ V to }30\text{ V DC}$ Reverse polarity protection
Current consumption	Typ. 40 mA
Output voltage	0 V to 10 V DC
Output loading	Max. 10 mA
Nonlinearity	1 %
Maximum speed	30,000 rpm
Temperature	-40 °C to +125 °C
Operating and storage	


Output type and electrical variant

φ_{FS}	360°	180°	90°	45°
Clockwise	VA	VB	VC	VD
Counterclockwise	VE	VF	VG	VH

Electrical output/shaft position



Connections



Part numbering

RMB30 IA 09B C 1

Output type

IA - Incremental, push-pull, 24 V
IB - Incremental, open collector, 24 V
IC - Incremental, RS422, 5 V
SC - Absolute binary synchro-serial (SSI), RS422, 5 V
SI - SSI and incremental, 5 V
Cx - Linear current:

Linear current output 4 - 20 mA, supply 20 V to 30 V DC				
	360°	180°	90°	45°
Clockwise	CA	CB	CC	CD
Counterclockwise	CE	CF	CG	CH

Vx - Linear voltage:

Linear voltage output 0 - 10 V, supply 20 V to 30 V DC				
	360°	180°	90°	45°
Clockwise	VA	VB	VC	VD
Counterclockwise	VE	VF	VG	VH

NOTE: Not all combinations are valid.

Special requirements*
1 - None (standard)

Shape
C - Circular

Resolution


For **IA**, **IB**, **IC**, **SC** and **SI** (counts or positions per revolution)

Decimal			Binary		
D32 - 320	D80 - 800	2D0 - 2000	07B - 128	10B - 1024	13B - 8192
D40 - 400	1D0 - 1000		08B - 256	11B - 2048	
D50 - 500	1D6 - 1600		09B - 512	12B - 4096	

For Cx and Vx

10B - 1024 counts per revolution


* For sample quantities of RMB30 supplied with a magnet please add "KIT" to the end of the required RMB30 part number, eg. RMB30IA09BC1KIT.



Series	Output type	Resolution	Shape	Special requirements
RMB30	Cx	10B	C	1
	Vx			
	IA	2D0 / 1D6 / 1D0 / D80 / D50 / D40 / D32 / 13B / 12B / 11B / 10B / 09B / 08B / 07B		
	IB			
	IC			
	SC			
	SI			

Magnetic actuator and magnet ordering information

Actuator for integration onto shaft



Shaft = Ø*h7

Fixing: Grub screw provided

* Hole diameter for nominal shaft size.
See table on the right for more
information on available shaft sizes.

Part numbers:


For resolutions up to 9 bit absolute (512 cpr incremental)

RMA04A2A00 – Ø4 mm shaft	RMA10A2A00 – Ø10 mm shaft
RMA05A2A00 – Ø5 mm shaft	RMA19A2A00 – Ø3/16" shaft
RMA06A2A00 – Ø6 mm shaft	RMA25A2A00 – Ø1/4" shaft
RMA08A2A00 – Ø8 mm shaft	RMA37A2A00 – Ø3/8" shaft

For resolutions from 10 bit absolute (800 cpr incremental) and above

RMA04A3A00 – Ø4 mm shaft	RMA10A3A00 – Ø10 mm shaft
RMA05A3A00 – Ø5 mm shaft	RMA19A3A00 – Ø3/16" shaft
RMA06A3A00 – Ø6 mm shaft	RMA25A3A00 – Ø1/4" shaft
RMA08A3A00 – Ø8 mm shaft	RMA37A3A00 – Ø3/8" shaft

Actuator for integration into shaft



Part numbers:

For resolutions up to 9 bit absolute (512 cpr incremental)

RMH06A2A00

For resolutions from 10 bit absolute (800 cpr incremental) and above

RMH06A3A00

With N-pole marker scribed to a ±5° accuracy:

For resolutions up to 9 bit absolute (512 cpr incremental)

RMH06A2A02


For resolutions from 10 bit absolute (800 cpr incremental) and above

RMH06A3A02

Hole = Ø6G7

Fixing: Glue (recommended – LOCTITE 648 or 2701)

Magnet for direct recessing in non-ferrous shafts



Part numbers:

For resolutions up to 9 bit absolute (512 cpr incremental)

RMM44A2A00 (individually packed) – for sample quantities only
RMM44A2C00 (packed in tubes)

For resolutions from 10 bit absolute (800 cpr incremental) and above

RMM44A3A00 (individually packed) – for sample quantities only
RMM44A3C00 (packed in tubes)

Fixing: Glue (recommended – LOCTITE 648 or 2701)

Head office

RLS merilna tehnika d.o.o.

Poslovna cona Žeje pri Komendi
Pod vrbami 2
SI-1218 Komenda
Slovenia

T +386 1 5272100

F +386 1 5272129

E mail@rls.si

www.rls.si

Document issues

Issue	Date	Page	Amendments done
09	23. 6. 2011	4, 5, 6	New product images
10	21. 5. 2014	4, 5, 6, 8	8 bit resolution option added to output types IC, SC and SI
		3	Other resolutions options added to the RMB30IA output
11	3. 3. 2017	1	RoHS added
		3, 4	IA and IB descriptions amended; IA 9-bit resolution deleted
		8	Cx and Vx resolution amended
		9	Ordering code amended, table added
12	18. 5. 2018	3 - 6	Resolutions amended
13	27. 7. 2018	General	Resolutions amended
14	8. 5. 2019	3, 4, 5, 6	RMB30IA, RMB30IB, RMB30IC, RMB30SC and RMB30SI power consumption amended
		7, 8	Temperature range for RMB30Cx and RMB30Vx / RMF44Vx amended
15	30. 8. 2019	2	Installation drawing amended
16	12. 2. 2020	3	Power supply amended

This product is not designed or intended for use outside the environmental limitations and operating parameters expressly stated on the product's datasheet. Products are not designed or intended for use in medical, military, aerospace, automotive or oil & gas applications or any safety-critical applications where a failure of the product could cause severe environmental or property damage, personal injury or death. Any use in such applications must be specifically agreed to by seller in writing, and is subject to such additional terms as the seller may impose in its sole discretion. Use of products in such applications is at buyer's own risk, and buyer will indemnify and hold harmless seller and its affiliates against any liability, loss, damage or expense arising from such use. Information contained in this datasheet was derived from product testing under controlled laboratory conditions and data reported thereon is subject to the stated tolerances and variations, or if none are stated, then to tolerances and variations consistent with usual trade practices and testing methods. The product's performance outside of laboratory conditions, including when one or more operating parameters is at its maximum range, may not conform to the product's datasheet. Further, information in the product's datasheet does not reflect the performance of the product in any application, end-use or operating environment buyer or its customer may put the product to. Seller and its affiliates make no recommendation, warranty or representation as to the suitability of the product for buyer's application, use, end-product, process or combination with any other product or as to any results buyer or its customer might obtain in their use of the product. Buyer should use its own knowledge, judgment, expertise and testing in selecting the product for buyer's application, end-use and/or operating environment, and should not rely on any oral or written statement, representation, or samples made by seller or its affiliates for any purpose. EXCEPT FOR THE WARRANTIES EXPRESSLY SET FORTH IN THE SELLER'S TERMS AND CONDITIONS OF SALE, SELLER MAKES NO WARRANTY EXPRESS OR IMPLIED WITH RESPECT TO THE PRODUCT, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE, WHICH ARE DISCLAIMED AND EXCLUDED. All sales are subject to seller's exclusive terms and conditions of sale which, where the seller is (a) RLS merilna tehnika d.o.o., are available at <https://www.rls.si/customer-service>, (b) Renishaw, Inc., are available at <http://www.renishaw.com/Shop/legal/en/-42186>, or (c) another person, are available on request, and in each case, are incorporated herein by reference, and are the exclusive terms of sale. No other terms and conditions apply. Buyer is not authorized to make any statements or representations that expand upon or extend the environmental limitations and operating parameters of the products, or which imply permitted usage outside of that expressly stated on the datasheet or agreed to in writing by seller.

RLS merilna tehnika d.o.o. has made considerable effort to ensure the content of this document is correct at the date of publication but makes no warranties or representations regarding the content. RLS merilna tehnika d.o.o. excludes liability, howsoever arising, for any inaccuracies in this document. © 2020 RLS d.o.o.