

RE22 rotary magnetic shaft encoder



The RE22 is a compact, high-speed rotary magnetic encoder designed for use in harsh environments. The traditional design allows for easy integration to existing machines.

A magnet is mounted to the shaft within the encoder body. Rotation of this magnet is sensed by a custom encoder chip within the body, and processed to give the required output format.

The encoder chip processes the signals received to provide resolutions of up to 13 bit (8,192 positions per revolution) with high operational speeds. Output signals are provided in industry standard absolute, incremental, analogue or linear formats.

The compact encoder body is just 22 mm in diameter and provides dirt immunity up to IP68.

The RE22 can be used in a wide range of applications including marine, medical, print, converting, industrial automation, metal working and instrumentation.

Product range

RE22AC - analogue with a single sine/cosine cycle per revolution

RE22BC - complementary analogue outputs with a single sine/cosine cycle per revolution


RE221C - incremental with 80 to 2,048 pulses per revolution (320 to 8,192 counts per revolution with x 4 evaluation)

RE22SC - synchro serial interface (SSI) with 320 to 8,192 positions per revolution

RE22Vx - linear voltage output in a range of variants



- Excellent immunity to IP68
- High speed operation to 20,000 rpm
- Compact - 22 mm diameter body
- Absolute - to 13 bit (8,192 ppr)
- Industry standard absolute, incremental, analogue and linear output formats
- Accuracy to $\pm 0.3^\circ$
- Simple integration

Storage and handling





IMPORTANT: Power to RE22 encoders must be supplied from a DC SELV supply complying with the essential requirements of EN (IEC) 60950 or similar specification.

The RE22 series encoders have been designed to the relevant EMC standards, but must be correctly integrated to achieve EMC compliance. In particular, attention to shielding arrangements is critical.



Connections




D' type connector - 9 way

| Pin nr. | RE22AC | | RE22BC | | RE22IC | | RE22SC | | RE22V | |
|---------|---------------------------------|-------------|---------------------------------|-------------|---------------------------------|-------------|---------------------------------|-------------|------------------|-------------|
| | Function | Wire colour | Function | Wire colour | Function | Wire colour | Function | Wire colour | Function | Wire colour |
| 1 | Shield - see connection diagram | | Shield - see connection diagram | | Shield - see connection diagram | | Shield - see connection diagram | | | |
| 2 | V _A | Green | V _{A+} | Green | Z | White | Clock | White | NC | - |
| 3 | V _B | Brown | V _{B+} | Brown | B | Green | Clock- | Brown | V _{out} | Green |
| 4 | NC | - | NC | - | A | Grey | NC | - | NC | - |
| 5 | V _{dd} | Red | V _{dd} | Red | V _{dd} | Red | V _{dd} | Red | V _{dd} | Red |
| 6 | NC | - | V _{A-} | Yellow | Z- | Brown | Data | Green | NC | - |
| 7 | NC | - | V _{B-} | White | B- | Yellow | Data- | Yellow | NC | - |
| 8 | NC | - | NC | - | A- | Pink | NC | - | NC | - |
| 9 | GND | Blue | GND | Blue | GND | Blue | GND | Blue | GND | Blue |


Installation drawing

Dimensions and tolerances in mm


IP64 / IP68 (axial cable exit)




IP53 (axial cable exit)



IP64/68 (radial cable exit)



IP53 (radial cable exit)



Special option 06

Flat, D-shaped shaft




Table of expected bearing life ratings in hours

| Speed (rpm) | Rad. load 5 N | Rad. load 10 N | Rad. load 15 N | Rad. load 20 N |
|-------------|---------------|----------------|----------------|----------------|
| 500 | 205,401 | 98,455 | 54,569 | 33,333 |
| 1,000 | 102,700 | 49,227 | 27,285 | 16,667 |
| 2,000 | 51,350 | 24,613 | 13,642 | 8,333 |
| 5,000 | 20,540 | 9,845 | 5,457 | 3,333 |
| 10,000 | 10,270 | 4,923 | 2,728 | 1,667 |
| 15,000 | 6,847 | 3,282 | 1,819 | 1,111 |
| 20,000 | 5,135 | 2,461 | 1,364 | 833 |


Maximum recommended shaft loads: radial 20N, axial 10N

RE22AC – Analogue sinusoidal outputs

2 channels V_A V_B sinusoids (90° phase shifted, single ended)

| | |
|---|---|
| Power supply | $V_{dd} = 5\text{ V} \pm 5\%$ |
| Power consumption | 20 mA |
| Outputs | Signal amplitude $2 \pm 0.2 V_{pp}$ Signal offset $\frac{V_{dd}}{2} \pm 5\text{ mV}$ |
| Max. output frequency | 333 Hz |
| Max. cable length | 3 m |
| Connector options | 'D' type connector - 9 way (standard) Flying lead |
| Temperature Operating and storage | -40 °C to +125 °C |
| Maximum speed | 20,000 rpm |
| Internal serial impedance | 720 Ω |

Timing diagram




V_A leads V_B by 90° for clockwise rotation of shaft

RE22BC – Analogue complementary sinusoidal outputs

2 channels V_A and V_B differential sinusoids in quadrature (90° phase shifted)

| | |
|---|---|
| Power supply | $V_{dd} = 5\text{ V} \pm 5\%$ |
| Power consumption | 20 mA |
| Outputs | Signal amplitude $0.5 \pm 0.1 V_{pp}$ Signal offset $\frac{V_{dd}}{2} \pm 5\text{ mV}$ |
| Max. output frequency | 333 Hz |
| Max. cable length | 20 m |
| Connector options | 'D' type connector - 9 way (standard) Flying lead |
| Temperature Operating and storage | -40 °C to +125 °C |
| Maximum speed | 20,000 rpm |
| Internal serial impedance | 100 Ω |

Timing diagram



V_A leads V_B by 90° for clockwise rotation of shaft

RE22IC – Incremental outputs

Square wave differential line driver to RS422


| | |
|--|--|
| Power supply | $V_{dd} = 5\text{ V} \pm 5\%$ |
| Power consumption | 35 mA |
| Output signals | A, B, Z, A-, B-, Z- (RS422) |
| Max. cable length | 50 m |
| Connector options | 'D' type connector - 9 way (standard) Flying lead |
| Temperature Operating and storage | -40 °C to +125 °C |
| Edge separation | Min. 1 μs |

| Resolution options (counts per revolution) | Maximum speed (rpm) | Accuracy* | Hysteresis |
|---|------------------------|-----------------|------------|
| 320, 400, 500 | 20,000 | $\pm 0.5^\circ$ | 0.18° |
| 512 | 20,000 | $\pm 0.5^\circ$ | 0.45° |
| 800, 1,000, 1,024 | 20,000 | $\pm 0.3^\circ$ | 0.18° |
| 1,600, 2,000, 2,048 | 10,000 | $\pm 0.3^\circ$ | 0.18° |
| 4,096 | 5,000 | $\pm 0.3^\circ$ | 0.18° |
| 8,192 | 2,500 | $\pm 0.3^\circ$ | 0.18° |


* Worst case within operational parameters including magnet position and temperature.

Timing diagram

Complementary signals not shown



Recommended signal termination



B leads A for clockwise rotation of shaft



RE22SC – Absolute binary synchro-serial interface (SSI)


Serial encoded absolute position measurement

| | |
|--|--|
| Output code | Natural binary |
| Power supply | $V_{dd} = 5\text{ V} \pm 5\%$ |
| Power consumption | 35 mA |
| Repeatability | $\leq 0.07^\circ$ |
| Data output | Serial data (RS422) |
| Data input | Clock (RS422) |
| Max. cable length | 100 m (at 1 MHz) |
| Connector options | 'D' type connector - 9 way (standard) Flying lead |
| Temperature Operating and storage | -40 °C to +125 °C |

| Resolution options (positions per revolution) | Maximum speed (rpm) | Accuracy* | Hysteresis |
|--|------------------------|-----------------|------------|
| 320, 400, 500 | 20,000 | $\pm 0.5^\circ$ | 0.18° |
| 512 | 20,000 | $\pm 0.5^\circ$ | 0.45° |
| 800, 1,000, 1,024 | 20,000 | $\pm 0.3^\circ$ | 0.18° |
| 1,600, 2,000, 2,048 | 10,000 | $\pm 0.3^\circ$ | 0.18° |
| 4,096 | 5,000 | $\pm 0.3^\circ$ | 0.18° |
| 8,192 | 2,500 | $\pm 0.3^\circ$ | 0.18° |

* Worst case within operational parameters including magnet position and temperature.


Timing diagram



Clock $\leq 900\text{ kHz}$ $16\ \mu\text{s} \leq t_m \leq 22\ \mu\text{s}$ (for 9 bit resolution)
 Clock $\leq 4\text{ MHz}$ $12.5\ \mu\text{s} \leq t_m \leq 20.5\ \mu\text{s}$ (for all other resolutions)

Recommended signal termination

For data output lines only



Position increases for clockwise rotation of shaft



A RENISHAW associate company

RE22Vx – Linear voltage output

| | |
|---|--|
| Power supply | $V_{dd} = 5\text{ V} \pm 5\%$ |
| Power consumption | 26 mA typical |
| Output voltage | 0 V to V_{dd} |
| Output loading | Max. 10 mA |
| Nonlinearity | 1 % |
| Max. cable length | 20 m |
| Connector options | 'D' type connector - 9 way (standard) Flying lead |
| Temperature Operating and storage | -40 °C to +125 °C |
| Maximum speed | 20,000 rpm |

Output type and electrical variant

| Φ_{FS} | 360° | 180° | 90° | 45° |
|------------------|-----------|-----------|-----------|-----------|
| Clockwise | VA | VB | VC | VD |
| Counterclockwise | VE | VF | VG | VH |

Electrical output/shaft position




Image shows clockwise rotation of shaft

Ordering code



Encoder part number
eg **RE22SC0409B10A3A00**

RE22 SC 04 09B 10 A 3 A 00

Output type

AC - Analogue sinusoidal 2 V_{pp}
BC - Analogue complementary sinusoidal
IC - Incremental, RS422
SC - Absolute binary synchro-serial (SSI), RS422
Vx - Linear voltage:

| Linear voltage output 0 V to 5 V, supply 5 V DC | | | | |
|---|-----------|-----------|-----------|-----------|
| | 360° | 180° | 90° | 45° |
| Clockwise | VA | VB | VC | VD |
| Counterclockwise | VE | VF | VG | VH |

Shaft size

04 - 4 mm

Resolution

For output types **AC** and **BC**:

01S - One sine/cosine wave per revolution

For output type **Vx**:

10B - 1,024 positions per revolution

For output types **IC** and **SC** (counts or positions per revolution):

| Decimal | | | Binary | |
|------------------|-------------------|-------------------|-------------------|-------------------|
| D32 - 320 | D80 - 800 | 2D0 - 2000 | 09B - 512 | 12B - 4096 |
| D40 - 400 | 1D0 - 1000 | | 10B - 1024 | 13B - 8192 |
| D50 - 500 | 1D6 - 1600 | | 11B - 2048 | |

Special requirements

00 - None
06 - With flat, D-shaped shaft
0M - Cable length in meters

Environment

A - IP53, Aluminium body (standard)
B - IP64, Aluminium body (for Body style 3 only)
C - IP68, Aluminium body (for Body style 3 only)

Body style and cable exit

2 - Cylindrical body, radial cable exit
3 - Cylindrical body, axial cable exit

Connector option

A - 'D' type connector - 9 way
F - Flying lead (no connector)

Cable length

10 - 1.0 meter (10 meters if **0M** is chosen)

NOTE: Not all combinations are valid.

Head office

RLS merilna tehnika d.o.o.

Poslovna cona Žeje pri Komendi
Pod vrbami 2
SI-1218 Komenda
Slovenia

T +386 1 5272100

F +386 1 5272129

E mail@rls.si

www.rls.si

Document issues

| Issue | Date | Page | Corrections made |
|-------|-------------|------|---|
| 1 | 13. 1. 2011 | - | New document |
| 2 | 9. 7. 2015 | 2 | Storage and handling info added; connections diagram and table added |
| | | 3 | Installation drawing tolerances updated, flat D-shaped shaft drawing added |
| | | 4-6 | Temperature range amended |
| | | 6 | Parallel output removed |
| | | 7 | Parallel output removed, resolution options updated and special option 06 added |