

AksIM-2

Off-Axis Rotary Absolute Redundant Magnetic Encoder


HIGH
ACCURACY

HIGH
SPEED

HIGH
SAFETY

The AksIM-2 redundant encoder is an advanced series of non-contact, high performance off-axis absolute encoders suitable for applications requiring a higher level of safety.

The AksIM-2 redundant encoder system consists of two identical, completely independent and electrically isolated encoder modules combined on one PCB and a separate axially magnetized ring.



The encoder is a redundant solution and part of the AksIM-2 absolute encoder range. For technical specifications not included in this document, refer to the latest version of MBD01 data sheet, available for download from the [AksIM-2 website](#).

Features and benefits

- ▶ Proven AksIM-2 true absolute encoder technology
- ▶ Redundant version for higher safety applications
- ▶ Simple installation and easy connection
- ▶ Resolutions up to 20 bits
- ▶ BiSS communication interface
- ▶ Excellent price-performance ratio



COLLABORATIVE ROBOTS



AGVs



GIMBALS



ROBOTIC JOINTS



AGRICULTURAL
AUTOMATION

General information

With its compact and innovative design, the AksIM-2 redundant encoder system allows easier installation and is available in two dimensions. Two encoder modules on one PCB give much more freedom in designing advanced motion control systems to monitor the encoder position via two independent channels.

The redundant AksIM-2 encoder is available with the advanced BiSS communication protocol with differential signaling (RS422).

With resolutions up to 20 bits and accuracy better than $\pm 0.05^\circ$, high performance is assured when the encoder is installed within the required tolerance. Even better accuracy can be achieved by using the encoder's self-calibration function. The encoder operates from -40°C to $+85^\circ\text{C}$.


Like our proven series of standard AksIM-2 encoders, the redundant AksIM-2 encoder has a built-in advanced self-monitoring function that continuously checks several internal parameters. Error, warning and other status reports are available via BiSS register access and are indicated by LEDs.

The redundant AksIM-2 encoders are compatible with the standard MRA039 and MRA053 AksIM-2 absolute magnetic rings, providing a reliable solution for a wide range of applications.


For more information, please see the MBD01 AksIM-2 data sheet, available for download on the [AksIM-2 website](#).

Choose your AksIM-2 redundant system

**MB039-R readhead and
MRA039 magnetic ring**



**MB053-R readhead and
MRA053 magnetic ring**



Storage and handling

Storage temperature



-40 °C to +85 °C

Operating temperature




-40 °C to +85 °C

Humidity




Up to 70 % non-condensing



This encoder system is a high performance metrology product and should be handled with the same care as any other precision instrument. The use of heavy duty industrial tools or exposure to strong magnets such as a magnetic base is unacceptable and carries the risk of irreparable damage to the product.

The magnetic ring should not be exposed to magnetic field densities higher than 50 mT on its surface, as this can damage the ring.

 **Readhead is ESD sensitive - handle with care.**
Do not touch electronic circuit, wires or sensor area without proper ESD protection or outside of ESD controlled environment.

Packaging

There are two packaging variants. Up to 20 systems are packed individually in an antistatic box. In case the order quantity is larger than 20 systems, parts are packed in antistatic plastic trays. Magnetic rings and readheads are packed separately.


Bulk packaging:

Readheads			Magnetic rings		
Part	Tray size	Box size	Part	Tray size	Box size
MB039-R	10 units per tray	10 trays per box	MRA039	10 units per tray	12 trays per box
MB053-R	6 units per tray		MRA053		


Dimensions and installation drawings

Dimensions and tolerances are in mm.


AksIM-2 redundant encoder assembly size 039




Detail A:




Readhead MB039 redundant




Magnetic ring MRA039




AksIM-2 redundant encoder assembly size 053




Detail A:



Readhead MB053 redundant



Magnetic ring MRA053



Technical specifications

System data

Reading type		Axial reading
Resolution	MB039	19 bit
	MB053	20 bit
Maximum speed		10,000 RPM (for higher speeds contact RLS)
Accuracy		±0.05°

Electrical data

Supply voltage (V_{DD})		4.5 V to 5.5 V at the connector. Rise time should be shorter than 20 ms.
Current consumption		2 × 135 mA (typ.)
Isolation		250 V _{AC}
Connection		Molex 503480-2000 (Right-Angle, with Flip Lock) FFC, 20-pin, 0.5 mm pitch, contacts on top and bottom side **

Environmental data

Operating and storage temperature		-40 °C to +85 °C (standard) *
--	--	-------------------------------



* For a wider temperature range please **contact RLS**.

** Cable can be flipped, in such case Primary and Secondary encoders are interchanged.

For more information, please see the **MBD01 AksIM-2 data sheet**, available for download on the [AksIM-2 website](#).

Electrical connections

Pin	Signal	Encoder
1	Chassis	Chassis
2	V_{DD}	V_{DD}
3	GND	GND
4	Clock+	Clock+
5	Clock-	Clock-
6	GND	GND
7	Data+	Data+
8	Data-	Data-
9	GND	GND
10	Not connected	
11	Not connected	
12	GND	GND
13	Data-	Data-
14	Data+	Data+
15	GND	GND
16	Clock-	Clock-
17	Clock+	Clock+
18	GND	GND
19	V_{DD}	V_{DD}
20	Chassis	Chassis




Readhead is ESD sensitive - handle with care.

Do not touch electronic circuit, wires or sensor area without proper ESD protection or outside of ESD controlled environment.

Part numbering

Readhead



Not all part number combinations are valid. Please refer to the table of available combinations below.

Series	Ring Compatibility	Communication Interface	Variant	Resolution	Shape	Connector	Option	Special requirements
MB	039	DC	C	19B	R	C	L	00
	053			20B				

Magnetic ring

	MRA	039	B	C	020	D	S	E	00
Series	MRA - AksIM magnetic ring								
Outer diameter and readhead compatibility	039 - 39 mm 053 - 53 mm								
Thickness	B - 2.0 mm								
Installation type	C - Countersunk fasteners								
Inner diameter	020 - 20 mm 030 - 30 mm								
Accuracy grade	D - $\pm 0.1^\circ$								
Material	S - Stamped metal plate with CPE rubber								
Zero marking	E - Engraved								
Special requirements	00 - No special requirements (standard)								


Not all part number combinations are valid. Please refer to the table of available combinations below.

Series	Outer diameter and readhead compatibility	Thickness	Installation type	Inner diameter	Accuracy grade	Material	Zero marking	Special requirements
MRA	039	B	C	020	D	S	E	00
	053			030				

Accessories



Cable assembly
ACC039



Breakout board
ACC040



Cable assembly
ACC015, ACC061



Cable assembly
ACC016



USB interface
E201-9S



Magnet viewer
MM0001

Cable assemblies

Part number	Length	Connector 1	Connector 2	Notes
ACC039	152 mm	FFC, 20 Cores, 0.5 mm pitch	FFC, 20 Cores, 0.5 mm pitch	Contacts on the same side
ACC040	PCB board	FFC, 20 Cores, 0.5 mm pitch	2x FCI 10114830-11108LF	For direct connection of ACC015 or ACC016
ACC061	3.0 m	FCI 10114826-00008LF and 10114827-002LF	Flying leads	Single-shielded
ACC015	1.0 m		DSUB-9 M	
ACC016				

The ACC039 cable assembly is for direct connection between the readhead and other electronic board. If a wired connection is required (for testing, etc.), an additional breakout board ACC040 is recommended along with ACC015 or ACC061 with split wires or ACC016 for direct connection to the USB interface E201.

For more information, please see the MBD01 AksIM-2 data sheet, available for download on the [AksIM-2 website](#).

Head office

RLS Merilna tehnika d.o.o.

Poslovna cona Žeje pri Komendi
Pod vrbami 2
SI-1218 Komenda
Slovenia

T +386 1 5272100

F +386 1 5272129

E mail@rls.si

www.rls.si

Global support

Visit our [website](#) to contact your nearest sales representative.

Date	Issue	Page	Description
24. 9. 2021	2	5, 7	Dimensions of the fasteners amended.
		12	ACC039, ACC040 and ACC061 added

This product is not designed or intended for use outside the environmental limitations and operating parameters expressly stated on the product's datasheet. Products are not designed or intended for use in medical, military, aerospace, automotive or oil & gas applications or any safety-critical applications where a failure of the product could cause severe environmental or property damage, personal injury or death. Any use in such applications must be specifically agreed to by seller in writing, and is subject to such additional terms as the seller may impose in its sole discretion. Use of products in such applications is at buyer's own risk, and buyer will indemnify and hold harmless seller and its affiliates against any liability, loss, damage or expense arising from such use. Information contained in this datasheet was derived from product testing under controlled laboratory conditions and data reported thereon is subject to the stated tolerances and variations, or if none are stated, then to tolerances and variations consistent with usual trade practices and testing methods. The product's performance outside of laboratory conditions, including when one or more operating parameters is at its maximum range, may not conform to the product's datasheet. Further, information in the product's datasheet does not reflect the performance of the product in any application, end-use or operating environment buyer or its customer may put the product to. Seller and its affiliates make no recommendation, warranty or representation as to the suitability of the product for buyer's application, use, end-product, process or combination with any other product or as to any results buyer or its customer might obtain in their use of the product. Buyer should use its own knowledge, judgment, expertise and testing in selecting the product for buyer's application, end-use and/or operating environment, and should not rely on any oral or written statement, representation, or samples made by seller or its affiliates for any purpose. EXCEPT FOR THE WARRANTIES EXPRESSLY SET FORTH IN THE SELLER'S TERMS AND CONDITIONS OF SALE, SELLER MAKES NO WARRANTY EXPRESS OR IMPLIED WITH RESPECT TO THE PRODUCT, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE, WHICH ARE DISCLAIMED AND EXCLUDED. All sales are subject to seller's exclusive terms and conditions of sale which, where the seller is (a) RLS Merilna tehnika d.o.o., are available at <https://www.rls.si/eng/salesterms>, (b) Renishaw, Inc., are available at <https://www.renishaw.com/legal/en/-42186>, or (c) another person, are available on request, and in each case, are incorporated herein by reference, and are the exclusive terms of sale. No other terms and conditions apply. Buyer is not authorized to make any statements or representations that expand upon or extend the environmental limitations and operating parameters of the products, or which imply permitted usage outside of that expressly stated on the datasheet or agreed to in writing by seller.

RLS Merilna tehnika d.o.o. has made considerable effort to ensure the content of this document is correct at the date of publication but makes no warranties or representations regarding the content. RLS Merilna tehnika d.o.o. excludes liability, howsoever arising, for any inaccuracies in this document. © 2021 RLS d.o.o.